

AT5.5X125TVE | AT.TVE - PROTWIST® 1000 Volt insulated screwdrivers for slotted-head screws



Description:

- For improved safety, each screwdriver is tested individually at 10,000 Volt for 10 seconds VDE approved.
- Slim Profile gives 27% more reach.
- Inline Hardening Process +100%
 Tip Life and +100% Bar Strength.
- Handle Material Softer for more Comfort and still Chemical Resistant.
- Handle 'Channel' +10% Torque.
- Laser Marking gives virtually Permanent Marking.
- CNC tip machining gives better Screw Fit increasing Torque Transfer and Reducing Wear.
- Milled blade: --> 5.5 mm included.
- Fillet blade: 6.5 --> 12 mm.

=	AT5.5X125TVE
Diameter [mm]	30.0
Length L [mm]	235.0
Length L1 [mm]	125.0
Length L2 [mm]	110.0
Length L3 [mm]	15.0