Product overview

as lighting, security or network modules.

Moulded in recyclable ABS UL94-V0

Recessed front face for overlay

Solid and vented versions available

(CRBS01 and CBRS02)

A range of versatile wall mountable enclosures,

available in two body types, three sizes and three

colours. The vented housing allows airflow, making them ideal for thermostats, environmental sensing and IoT applications. The solid housing lends itself to wall mount controls and smart applications such

Front and back clip together construction (tool required for disassembly once mounted)
Internal PCB mount pillars moulded into the front and back sections of the housing (Pi A+ fits base

of CBRS02, no PCB mounts in back of CBRS03) • Internal clips moulded into fronts for snap-in PCB (Arduino fits CBRS02 and Thunder Sense fits

Room sensor enclosures

268 HANDHELD CASES

292 UNIVERSAL ENCLOSURES

318 HEAVY DUTY AND ELECTRICAL ENCLOSURES

342 DESKTOP AND INSTRUMENT

348 DEVELOPMENT BOARD ENCLOSURES



370 CUSTOM SIZED ENCLOSURES

UK-plug back box (CBRS01)
Sizes to house standard batteries: PP3-9V & AA in CBRS01 & CBRS02, CR3032 Coin-Cell in CBRS03

Rear knockout for cable entry (20mm diameter)Multiple mounting options, including single gang

• Recesses in rear face for additional labelling


- Three colour options: white RAL9003, light grey RAL7047 and black RAL9005
- Manufactured in the UK

CBRS03)

CBRSOTWHH	CBRS02SGY

SPECIFICATION	
Materials	ABS UL94-VO
Operating temperature	-10°C to + 70°C
Standard unit includes	Enclosure lid Enclosure base

WHITE	BLACK	GREY	SIZE	STYLE	LENGTH	WIDTH	HEIGHT
CBRS01SWH	CBRS01SBK	CBRS01SGY	1	Solid	86mm	86mm	25.5mm
CBRS01VWH	CBRS01VBK	CBRS01VGY	1	Vented	86mm	86mm	25.5mm
CBRS02SWH	CBRS02SBK	CBRS02SGY	2	Solid	74mm	74mm	25.5mm
CBRS02VWH	CBRS02VBK	CBRS02VGY	2	Vented	74mm	74mm	25.5mm
CBRS03SWH	CBRS03SBK	CBRS03SGY	3	Solid	51mm	51mm	25.5mm
CBRS03VWH	CBRS03VBK	CBRS03VGY	3	Vented	51mm	51mm	25.5mm



KEY FEATURES

Smart electronics enclosure | No screws needed | Easy wall mounting





+44 (0)1638 716101 | sales@camdenboss.com | www.camdenboss.com We operate a constant improvement policy, our products are subject to change without notice.

Vers 3