



SlimView Group Lock Box

Part Number: 151761

Overview

The SlimView™ Group Lock Box reduces the space you need for group lockout or box storage with a slim profile and recessed door that allows padlocks to hang straight.

- Yellow color is ideal for contractors or whenever you need to identify different groups of workers quickly
- Rugged steel body and polycarbonate door stand up to all of your toughest jobs
- Clear door gives you clear view into everything you need during your group lockout
- Convenient storage with built-in padlock and key hangers
- Room for a dozen—storage space for up to 12 padlocks
- Easy to wall mount with button mount holes

Specifications

Key Characteristics	Product Number	151761
	UPC	888434559024
	UOM	Each
	Trade Name	SlimView™
	Brand Name	Brady®
	Country of Origin	China
	HTS Code (Harmonized Tariff Schedule)	3926.90.9985
	ECCN (Export Commodity Control Number)	EAR99
Dimensions	Dimensions	6.25 in H x 10.5 in W x 3.125 in D
	Height	6.25 in
	Width	10.5 in
	Depth	3.125 in
Material Characteristics	Material Number	LOTO-97 (View Technical Data Sheet)
	Material	Heavy Duty Steel with Polycarbonate Cover
	Coating Material	Powder Coated
	Lockout Box Material	Steel
	Color	Yellow
	Service Temperature Range °F	-40 °F - 248 °F
	Minimum Service Temperature °F	-40 °F
	Maximum Service Temperature °F	248 °F
	Steel Type	Heavy-Duty
Product Features	Application	Lockout Tagout
	Cabinet Mounting Type	Portable, Wall Mounted
	Lockout Box Type	Portable - Empty
	Maximum Number of Padlocks	12
	Maximum Number of Padlocks Stored	12
	Number of Hooks	6
	Wall-Mountable?	Yes
Compatibility	Maximum Shackle Diameter	0.33 in
Compliance	UNSPSC	46171509
	RoHS Compliance Status	Compliant with Directive 2011/65/EU and 2015/863