

# Wiha Rapid System.

Quick and Professional.



Drilling, countersinking, driving screws and cutting threads is child's play with the Wiha Rapid System. The innovative RapidFix quick-release holder forms the basis for a variety of hex drive tools.

With Rapid System, Wiha once again demonstrates that the user is central. The trend towards battery-powered drivers is continuing undiminished. Efficient models are greatly increasing the number of application areas and enabling more flexible working. The Wiha Rapid System also opens these application areas to professional use.

With the new RapidFix quick-release holder, Wiha closes the gap between the chuck of the battery-powered drivers and the quick-release holder for driver bits. The RapidFix holder allows rapid tool change, provides a secure fit and meets the greater requirements as regards concentricity and retention forces.



Flexible, easy and quick – drill, countersink and turn screws with the Wiha Rapid System for wood ...



... or with the Wiha Rapid System for metal.



Wiha Rapid System:

- Quick  
Saves time when changing tools
- Secure  
Fixed connection between tool insert and holder
- Zero-play  
For exact boreholes
- Universal  
Fits all 1/4" hex drives

## RapidFix - One For All.



**7148**

RapidFix Quick-release Holder, Style E 6.3.

Sleeve: Metal, coated.

Suitable for: DIN 3126 ISO 1173 Style D 6.3 + F 6.3 and double bits.

Drive: DIN 3126 ISO 1173 Style E 6.3.

Application: Whenever the bit needs a secure and zero-play hold. Optimised for the use of drill bits.

Extra: Due to the special holding mechanism, this bit holder holds all types of bits with 1/4" hex drive.

The play between bit and holder is reduced to a minimum.

Real single-handed operation for fast bit exchange.

Order-No.	1/4	1/4	60	10	£
24769 0	1/4	1/4	60	10	16.10



# Wiha Drill Bits.

Just Keep on Working.

## Wood Twist Drill Bit.



**7804** Wood Twist Drill Bit, Style C 6.3.  
 Material: High grade chrome-molybdenum steel, ground.  
 Drive: With 1/4" hex shank according to DIN 3126 C 6.3.  
 Application: Especially suitable for boreholes in soft and hardwoods, as well as in veneered and coated laminated materials.  
 Extra: By means of careful rough-cutting, drilling of pocket holes is easy and does not tear the material.  
 With centring tip for exact drilling.  
 Particularly suitable for use in battery-powered drivers.

Order-No.	⊗	↔	↔	⊙	⊖	£
27873 1	3.0	70	36	1/4	10	8.05
27876 2	4.0	75	43	1/4	10	8.15
27877 9	5.0	85	56	1/4	10	8.70
27879 3	6.0	95	66	1/4	10	9.25
27880 9	8.0	110	81	1/4	10	11.80
27881 6	10.0	110	81	1/4	10	14.30



**79184 T19** Wood Twist Drill Set, 19 pcs.  
 Pouch: High-quality nylon pouch, 13 x 2 x 10 cm.  
 Bits: 25 mm standard and torsion bits, wood twist drill bits, countersink bit.  
 Holder: RapidFix Quick-release Holder, Style E 6.3.  
 Application: Compact range for drilling, countersinking and driving screws in wood.  
 Extra: Pouch with sturdy metal belt clip.

Order-No.	Series	⊖	£
28024 6	79184 T19	1	90.00
⊗	7804	1x3.0 1x4.0 1x5.0 1x6.0 1x8.0	
⊙	7806	1x12.4	
⊕	7011 ZOT	1xPH2	
⊕	7012 ZOT	1xPZ1 3xPZ2 1xPZ3	
⊗	7015 Z	1xT15 1xT20 1xT25 1xT30	
⊙	7019 Z SIT	1xSIT 20 1xSIT 30	
⊙	7148	RapidFix	

**7918 TL** Nylon Pouch, Empty.

Order-No.	Series	⊖	£
28028 4	7918 TL	1	10.00

NEW

**79184 T19 VH1** Wood Twist Drill Sets in Carton Display.

Order-No.	Content	⊖	£
30397 6	5 x 79184 T19	1	427.00

## Twist Drill Bit.



**7805** Twist Drill Bit, Style C 6.3.  
 Material: High-quality HSS steel, ground.  
 Drive: With 1/4" hex shank according to DIN 3126 C 6.3.  
 Application: Universal application in metal, plastic and wood.  
 Extra: Particularly suitable for use in battery-powered drivers.  
 Special rivet-hole sizes 3.1, 4.1 and 5.1.

Order-No.	⊗	↔	↔	⊙	⊖	£
27882 3	3.0	38	16	1/4	10	3.70
28055 0	3.1	38	16	1/4	10	3.70
27883 0	3.3	40	18	1/4	10	3.70
27884 7	4.0	43	22	1/4	10	3.80
28056 7	4.1	43	22	1/4	10	3.80
27885 4	4.2	43	22	1/4	10	3.85
27886 1	5.0	48	26	1/4	10	3.90
28057 4	5.1	48	26	1/4	10	3.85
27887 8	6.0	48	26	1/4	10	4.10
27888 5	6.8	48	30	1/4	10	4.15
27889 2	8.0	50	32	1/4	10	4.70
27890 8	8.5	51	34	1/4	10	4.75
27891 5	10.0	54	37	1/4	10	5.40



**79185 T19** Twist Drill Set, 19-pcs.  
 Pouch: High-quality nylon pouch, 13 x 2 x 10 cm.  
 Bits: 25 mm standard and torsion bits, twist drill bits.  
 Holder: RapidFix Quick-release Holder, Style E 6.3.  
 Application: Compact assortment for universal application when driving screws.  
 Extra: Pouch with sturdy metal belt clip.

Order-No.	Series	⊖	£
28025 3	79185 T19	1	53.10
⊗	7805	1x3.0 1x4.0 1x4.2 1x5.0 1x6.0 1x8.0	
⊕	7011 ZOT	2xPH1 3xPH2 1xPH3	
⊕	7012 ZOT	2xPZ2	
⊗	7015 Z	1xT15 1xT20 1xT25 1xT30	
⊙	7148	RapidFix	

NEW

**79185 T19 VH1** Twist Drill Sets in Carton Display.

Order-No.	Content	⊖	£
30398 3	5 x 79185 T19	1	255.00