

## Han L32 B-HTE-HC-DL-M50



Image is for illustration purposes only. Please refer to product description.

Part number	19 30 132 0429
Specification	Han L32 B-HTE-HC-DL-M50
HARTING eCatalogue	<a href="https://b2b.harting.com/19301320429">https://b2b.harting.com/19301320429</a>

### Identification

Category	Hoods/Housings
Series of hoods/housings	Han <sup>®</sup> B
Type of hood/housing	Hood

### Version

Size	L32 B
Version	Top entry
Cable entry	1x M50
Locking type	Double locking lever
Field of application	Standard hoods/housings for industrial connectors

### Technical characteristics

Limiting temperature	-40 ... +125 °C
Degree of protection acc. to IEC 60529	IP65
Type rating acc. to UL 50 / UL 50E	4
	4X
	12

### Material properties

Material (hood/housing)	Aluminium die-cast
Surface (hood/housing)	Powder-coated
Colour (hood/housing)	RAL 7037 (dust grey)
RoHS	compliant
ELV status	compliant



Pushing Performance

## Material properties

China RoHS	e
REACH Annex XVII substances	No
REACH ANNEX XIV substances	No
REACH SVHC substances	No
California Proposition 65 substances	No

## Specifications and approvals

Approvals	DNV GL
CE	Yes

## Commercial data

Packaging size	1
Net weight	305 g
Country of origin	China
European customs tariff number	85389099
eCl@ss	27440202 Shell for industrial connectors