ELECTRICAL TEST KITS

RT250KIT

• RT250 is an electrical receptacle tester with LCD that

identifies common wiring faults on North American

the wiring fault, and the time required to trip a GFCI

NCVT-3P Dual Range Non-contact Voltage Tester with

Flashlight detects low and standard voltage from 12

to 1000 V AC or 70 to 1000V AC for a broad range of

• Includes all required batteries, manuals, and a pouch.

120V outlets. The LCD displays the voltage, identifies

KLEIN

2m CATIV CE

CAT II 135V

Best-Sellers in Convenient Value Kits



- CL320 HVAC Clamp Meter is an Auto-Ranging, TRMS digital clamp meter that measures 400A AC, DC Microamps, and Temperature. It comes with test leads with CAT III/CAT IV safety caps, and a K-Type thermocouple probe. CE
- IR07 is a dual IR (infrared) and probe thermometer that measures temperature from -40 to 572°F (-40 to 300°C). The IR probe accurately measures surface temperature with a distance to spot ratio of 8:1. The probe measures air and liquid temperature. Calculates differential temperature (T1-T2).
- NCVT-3P Dual Range Non-contact Voltage Tester with Flashlight detects low and standard voltage from 12 to 1000 V AC or 70 to 1000V AC for a broad range of applications.

CATIV CE <u>\$</u>2 m

Includes all required batteries, manuals, and a pouch.









			_			
Cat. No.	UPC# 0-92644+	Description	CL320 Clamp Meter with Test Leads & Thermocouple	<mark>IR07</mark> Dual IR/Probe Thermometer	RT250 GFCI Receptacle Tester with LCD	NCVT-3P Dual Range NCVT with Flashlight
CL320KIT	69349-6	HVAC Kit	٠	٠	-	•
RT250KIT	69350-2	Premium Electrical Test Kit	-	-	•	•

▲ Visit www.kleintools.com for warnings and instructions.

See our complete line of Test & Measurement www.kleintools.com

f 🕞 🎷 🙆

device.

applications.

colnshire II 60069

