TE Internal #: 1-2267795-3

Pluggable I/O Cable Assemblies, Pluggable / Direct Attach,

24AWG Wire Size, .25mm² Wire Size, Cable Assembly Length .984

ft [.3 m], Black

View on TE.com >



Cable Assemblies > Copper Cable Assemblies > Pluggable I/O Cable Assemblies











Pluggable I/O Cable Assembly Type: Pluggable / Direct Attach

Wire Size: .25 mm²

Pluggable I/O Cable Assembly Shielded: No

Cable Assembly Length: .3 m [.984 ft]

Features

Product Type Features

Latching Style	Pull Tab Release
Product Type	Cable Assembly
Product Designation	Patch Cord
Cable Assembly Category	Industry Standard
Pluggable I/O Cable Assembly Type	Pluggable / Direct Attach
Pluggable I/O Cable Assembly Shielded	No
Pluggable I/O Cable Assembly Cable Style	Discrete Pairs

Configuration Features

Configuration	Double-Ended
Number of Power Positions	0
Pluggable I/O Cable Assembly Keyed	No

Body Features

Contact Features

Contact Mating Area Plating Material	Gold
--------------------------------------	------



Mechanical Attachment

Jackscrew	Without
Housing Features	
Housing Material	Thermoplastic
Dimensions	
Wire Size	.25 mm ²
Operation/Application	
Halogen Free	No
Other	
Cable Assembly Length	.3 m[.984 ft]

Product Compliance

For compliance documentation, visit the product page on TE.com>

EU RoHS Directive 2011/65/EU	Compliant
EU ELV Directive 2000/53/EC	Compliant
China RoHS 2 Directive MIIT Order No 32, 2016	No Restricted Materials Above Threshold
EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JUL 2021 (219) Candidate List Declared Against: JUL 2021 (219) Does not contain REACH SVHC
Halogen Content	Not Low Halogen - contains Br or Cl > 900 ppm.
Solder Process Capability	Not reviewed for solder process capability

Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) 'Guidance on requirements for substances in articles' posted at this URL: https://echa.europa.eu/guidance-documents/guidance-on-reach

Compatible Parts







Documents

Product Drawings

CA, MTE FOW-FOW, 4POS, 300mm 15Au, 24AWG

English

CAD Files

3D PDF

3D

Customer View Model

ENG_CVM_CVM_1-2267795-3_A.2d_dxf.zip

English

Customer View Model

ENG_CVM_CVM_1-2267795-3_A.3d_igs.zip

English

Customer View Model

ENG_CVM_CVM_1-2267795-3_A.3d_stp.zip

English

By downloading the CAD file I accept and agree to the **Terms and Conditions** of use.

Datasheets & Catalog Pages

Datasheet - Ampmodu Mte Off-The Shelf Cable Assemblies

English

Circular Plastic Connectors Standard Cable Assemblies

English

Product Specifications

Application Specification

English