

KERN ACJ300-4M



The bestseller in analytical balances, with high-quality single-cell weighing system, also with EC type approval [M]



Verification by KERN possible:	yes
Verification class:	I
Verification value [e]:	1 mg

Counting

Counting resolution:	320000
Minimum piece weight at piece counting (Laboratory):	1 mg
Minimum piece weight at piece counting (Normal):	10 mg
Reference weight:	yes

Functions

Counting function:	yes
Function to save totals:	yes
Percentage determination:	yes
Standby function:	yes
Weighing with tolerance range:	yes

Environmental conditions

Maximum humidity:	85 %
Maximum operating temperature:	30 °C
Minimum ambient temperature:	10 °C
Minimum humidity:	20 %

Power supply

Input voltage:	110 V - 230 V AC
Mains adapter:	Mains adapter external
Mains adapter/adapter included:	EURO CH UK US

Services (optional)

DAkkS Certificate:	963-101
Verification:	965-201

Category

Brand:	KERN
Category:	Balances
Product Group:	Analytical balance

Packaging & shipping

Delivery:	24 h
Dimensions packaging (WxDxH):	390 x 570 x 530 mm
Gross weight:	8,970 kg
Net weight:	6,440 kg
Shipping method:	Parcel service

Measuring system

Adjustment options:	Internal calibration (manual) Internal calibration (auto)
Linearity:	0,300 mg
Minimum weight (USP):	400 mg
Readability [d]:	0,100 mg
Repeatability:	0,200 mg
Resolution:	3.200.000
Stabilisation time under laboratory conditions:	3 s
Warm up time:	8 h
Weighing capacity [Max]:	320 g
Weighing units:	g ct mg

Display

Display digit height (large):	1,400 cm
-------------------------------	----------

Technical data about verification

Minimum load [Min]:	10 mg
Periodic Verification for Italy:	969-112
Verification approval conforming to 2014/31/EU:	yes

KERN ACJ300-4M



The bestseller in analytical balances, with high-quality single-cell weighing system, also with EC type approval [M]

Construction


Dimensions draft shield (WxDxH):	201 x 220 x 256 mm
Dimensions housing (WxDxH):	210 x 340 x 325 mm
Level indicator:	yes
Material weighing plate:	stainless steel
Revolving screw feet:	yes
Weighing space (WxDxH):	174 x 162 x 227 mm
Weighing surface (d):	91

Piktogramme

STANDARD



OPTION



FACTORY

