

KERN CCS6K-6

Counting system to count the smallest parts in the largest quantities, counting resolution up to 999,999 points



Measuring system

Adjustment options:	External calibration
Linearity:	5 mg
Repeatability:	2 mg
Stabilisation time under laboratory conditions:	2 s
Weighing system:	Strain gauge
Weighing units:	g

Display

Display digit height (large):	2 cm
-------------------------------	------

Counting

Counting resolution:	1200000
Minimum piece weight at piece counting (Laboratory):	5 mg
Minimum piece weight at piece counting (Normal):	50 mg
Reference weight:	yes

Functions

Conversion function:	yes
Counting function:	yes
Function to save totals:	yes
PRE-TARE function:	yes
Weighing with tolerance range:	yes

Environmental conditions

Maximum humidity:	80 %
Maximum operating temperature:	40 °C
Minimum ambient temperature:	0 °C
Minimum humidity:	0 %

Power supply

Charging time:	12 h
Input voltage:	220 V - 240 V AC 50 Hz
Mains adapter:	Mains adapter external
Mains adapter/adapter included:	EURO CH UK US
Operating time (Backlight off):	60 h
Operating time (Backlight on):	40 h
Rechargeable battery:	Rchrg. battery optional

Services (optional)

Adjustment at the location of installation: abhängig von Auflösung/Max | depends on resolution and capacity

DAkkS Certificate:	962-128-127
--------------------	-------------

Category

Brand:	KERN
Product Group:	Counting system

Packaging & shipping


Delivery:	48 h
Dimensions packaging (WxDxH):	315 x 310 x 245 mm
Gross weight:	9,660 kg
Net weight:	6,210 kg
Shipping method:	Parcel service

Construction

Cable length:	1,500 m
Cable length of display device:	5 m
Casing material:	Plastic
Dimensions of weighing plate (WxDxH):	230 x 230 x 100 mm
Level indicator:	yes
Material weighing plate:	stainless steel
Revolving screw feet:	yes
Weighing surface (WxD):	230 x 230 mm

Piktogramme

STANDARD



OPTION

