

# KERN CFS300-3



Professional, high-resolution counting balance with 100 item memories and second balance interface, counting resolution up to 75,000 points



## Environmental conditions

Maximum humidity:	80 %
Maximum operating temperature:	40 °C
Minimum ambient temperature:	0 °C
Minimum humidity:	0 %

## Power supply

Charging time:	14 h
Input voltage:	110 V - 230 V AC
Mains adapter:	Mains adapter external
Mains adapter/adaptor included:	EURO CH UK US
Operating time (Backlight off):	70 h
Operating time (Backlight on):	40 h
Rechargeable battery:	Rchrg. battery optional

## Services (optional)

DAkkS Certificate:	963-127
--------------------	---------

## Category

Brand:	KERN
Category:	Balances
Product Group:	Counting scale

## Packaging & shipping

Delivery:	24 h
Dimensions packaging (WxDxH):	630 x 545 x 225 mm
Gross weight:	5,500 kg
Net weight:	2,500 kg
Shipping method:	Parcel service

## Construction

Casing material:	Plastic
Dimensions device (WxDxH):	320 x 350 x 125 mm
Dimensions draft shield (WxDxH):	167 x 154 x 80 mm
Dimensions housing (WxDxH):	315 x 350 x 180 mm
Dimensions of display device (WxDxH):	320 x 350 x 120 mm
Level indicator:	yes
Material weighing plate:	stainless steel
Overall dimensions mounted (WxDxH):	315 x 350 x 180 mm
Revolving screw feet:	yes
Weighing space (WxDxH):	158 x 143 x 64 mm
Weighing surface (d):	80

## Measuring system

Adjustment options:	External calibration
Linearity:	4 mg
Readability [d]:	1 mg
Recommended adjusting weight:	200 g (F1); 100 g (F1)
Repeatability:	2 mg
Resolution:	300000
Stabilisation time under laboratory conditions:	2 s
Tare range:	300 g
Warm up time:	2 h
Weighing capacity [Max]:	300 g
Weighing system:	Strain gauge
Weighing units:	g

## Display

Display digit height (large):	2 cm
-------------------------------	------

## Counting

Counting resolution:	60000
Minimum piece weight at piece counting (Laboratory):	5 mg
Minimum piece weight at piece counting (Normal):	50 mg
Reference weight:	yes

## Functions

Conversion function:	yes
Counting function:	yes
Function to save totals:	yes
PRE-TARE function:	yes
Weighing with tolerance range:	yes

# KERN CFS300-3



Professional, high-resolution counting balance with 100 item memories and second balance interface, counting resolution up to 75,000 points

## Piktogramme

### STANDARD



### OPTION



### FACTORY

