

KERN CKE2000-2



Easy to use, self-explanatory counting scale with laboratory accuracy, counting resolution up to 360,000 points



Power supply

Charging time:	10 h
Input voltage:	220 V - 240 V AC 50 Hz
Mains adapter:	Mains adapter external
Mains adapter/adaptor included:	EURO CH UK US
Operating time (Backlight off):	50 h
Operating time (Backlight on):	25 h
Rechargeable battery:	Rchrg. battery optional

Services (optional)

DAkkS Certificate:	963-127
--------------------	---------

Category

Brand:	KERN
Category:	Balances
Product Group:	Counting scale

Packaging & shipping

Delivery:	24 h
Dimensions packaging (WxDxH):	360 x 230 x 180 mm
Gross weight:	2,200 kg
Net weight:	1,800 kg
Shipping method:	Parcel service

Construction

Casing material:	Plastic
Dimensions housing (WxDxH):	167 x 250 x 85 mm
Material weighing plate:	stainless steel
Weighing surface (WxD):	150 x 170 mm

Piktogramme

STANDARD



OPTION



Measuring system

Adjustment options:	External calibration
Linearity:	30 mg
Readability [d]:	10 mg
Recommended adjusting weight:	2 kg (F1)
Repeatability:	10 mg
Resolution:	200000
Stabilisation time under laboratory conditions:	3 s
Tare range:	2 kg
Warm up time:	2 h
Weighing capacity [Max]:	2 kg
Weighing system:	Strain gauge
Weighing units:	g

Display

Display digit height (large):	9 mm
-------------------------------	------

Counting

Counting resolution:	200000
Minimum piece weight at piece counting (Laboratory):	10 mg
Minimum piece weight at piece counting (Normal):	100 mg

Functions

Counting function:	yes
Suspended weighing:	Hook

Environmental conditions

Maximum humidity:	80 %
Maximum operating temperature:	40 °C
Minimum ambient temperature:	10 °C