
KERN CKE 360-3







Measuring system	
Adjustment options:	External calibration
Linearity:	5 mg
Readability [d]:	1 mg
Recommended adjusting weight:	200 g (F1); 100 g (F1)
Repeatability:	1 mg
Resolution:	360000
Stabilisation time under laboratory conditions:	3 s
Tare range:	360 g
Warm up time:	2 h
Weighing capacity [Max]:	360 g
Weighing system:	Strain gauge
Weighing units:	g

Display digit height (large):	9 mm
Counting	
Counting resolution:	360000
Mininum piece weight at piece counting (Laboratory:	1 mg
Mininum piece weight at piece counting (Normal):	10 mg

Display

Functions	
Counting function:	yes
Suspended weighing:	Hook
Environmental conditions	
Maximum humidity:	80 %

Maximum operating temperature:

Minimum ambient temperature:

 $40\,^{\circ}\text{C}$

10 °C

Power supply	
Charging time:	10 h
Input voltage:	100 V - 240 V 50 / 60 Hz
Mains adapter:	Mains adapter external
Mains adapter/adapter included:	EURO CH UK US
Operating time (Backlight off):	30 h
Operating time (Backlight on):	15 h
Rechargeable battery:	Rchrg. battery optional

DAkkS Certificate:	963-127	
Category		
Dec. 1	KEDNI	

Services (optional)

0 ,	
Brand:	KERN
Category:	Balances
Product Group:	Counting scale

Packaging & shipping	
Delivery:	24 h
Dimensions packaging (WxDxH):	360 x 230 x 180 mm
Gross weight:	2,200 kg
Net weight:	1 kg
Shipping method:	Parcel service
UN number:	3496

Plastic
106 42
167 x 250 x 85 mm
yes
plastic
167 x 250 x 123 mm
yes
90 40
81

Piktogramme

STANDARD



OPTION

