

KERN EOB35K10



Allround parcel scale with robust stainless steel weighing plate - also with XL platform and large weighing ranges



Services (optional)

Adjustment at the location of installation: 961-248

DAkKS Certificate: 963-128

Category

Brand: KERN

Category: Balances

Packaging & shipping

Delivery: 24 h

Dimensions packaging (WxDxH): 370 x 365 x 145 mm

Gross weight: 5 kg

Net weight: 3,690 kg

Shipping method: Parcel service

Construction

Cable length of display device: 1,800 m

Dimensions of display device (WxDxH): 235 x 114 x 51 mm

Dimensions of weighing plate (WxDxH): 315 x 305 x 57 mm

Material weighing plate: stainless steel

Piktogramme

STANDARD



OPTION



Measuring system

Adjustment options: External calibration

Linearity: 20 g

Readability [d]: 10 g

Recommended adjusting weight: 20 kg (M2)

Repeatability: 10 g

Resolution: 3500

Tare range: 35 kg

Warm up time: 10 min

Weighing capacity [Max]: 35 kg

Weighing system: Strain gauge

Weighing units: lb kg PCS

Display

Display digit height (large): 2,500 cm

Functions

Data hold function: yes

Vibration-free weighing (Animal weighing program): yes

Environmental conditions

Maximum humidity: 80 %

Maximum operating temperature: 35 °C

Minimum ambient temperature: 5 °C

Power supply

Battery: 4x1.5 V AA

Input voltage: 100 V - 240 V 50 / 60 Hz

Mains adapter: Mains adapter external

Mains adapter/adaptor included: EURO CH UK US

Operating time: 60 h