

KERN HCB1T-3

Handy scales for higher loads

KERN[®]



Measuring system

Adjustment options:	External calibration
Linearity:	4 kg
Precision (of [Max]):	0,500 %
Readability [d]:	2 kg
Recommended adjusting weight:	500 kg (M1)
Repeatability:	2 kg
Resolution:	500
Stabilisation time under laboratory conditions:	2 s
Warm up time:	10 min
Weighing capacity [Max]:	1 t
Weighing system:	Strain gauge
Weighing units:	lb N kg

Display

Display digit height (large):	1,200 cm
-------------------------------	----------

Functions

Data hold function:	yes
---------------------	-----

Environmental conditions

Maximum humidity:	80 %
Maximum operating temperature:	35 °C
Minimum ambient temperature:	5 °C

Power supply

Battery:	3x1.5 V AA
Operating time:	300 h

Services (optional)

Adjustment at the location of installation: 961-250

DAkkS Certificate:	963-130H
--------------------	----------

Category

Brand:	KERN
Product Group:	Hanging scale

Packaging & shipping

Delivery:	24 h
Dimensions packaging (WxDxH):	215 x 150 x 85 mm
Gross weight:	880 g
Net weight:	356 g
Shipping method:	Parcel service

Construction

Casing material:	Plastic
Dimensions housing (WxDxH):	82 x 48 x 153 mm

KERN HCB1T-3

Handy scales for higher loads



Piktogramme

STANDARD



OPTION

