

# KERN HCD60K-2

High-resolution hanging scale for loads up to 300 kg



## Environmental conditions

Maximum humidity:	80 %
Maximum operating temperature:	40 °C
Minimum ambient temperature:	5 °C

## Power supply

Battery:	4x1.5 V AA
Charging time:	12 h
Operating time:	100 h
Operating time (Backlight off):	50 h
Operating time (Backlight on):	20 h
Rechargeable battery:	Rchrg. battery optional

## Services (optional)

Adjustment at the location of installation: 961-249

DAkkS Certificate:	963-129H
--------------------	----------

## Category

Brand:	KERN
Category:	Balances
Product Group:	Crane scale

## Packaging & shipping


Delivery:	24 h
Dimensions packaging (WxDxH):	285 x 225 x 140 mm
Net weight:	1,060 kg
Shipping method:	Parcel service

## Construction

Casing material:	Plastic
Dimensions housing (WxDxH):	150 x 79 x 97 mm
Dimensions of display device (WxDxH):	150 x 79 x 97,7 mm
Overall dimensions mounted (WxDxH):	150 x 276 x 79 mm

## Piktogramme

### STANDARD



### OPTION



## Measuring system

Adjustment options:	External calibration
Linearity:	40 g
Precision (of [Max]):	0,200 %
Readability [d]:	20 g
Recommended adjusting weight:	50 kg (M1)
Repeatability:	20 g
Resolution:	3000
Stabilisation time under laboratory conditions:	2 s
Warm up time:	10 min
Weighing capacity [Max]:	60 kg
Weighing system:	Strain gauge
Weighing units:	lb N kg

## Display

Display digit height (large):	2,800 cm
-------------------------------	----------

## Functions

Data hold function:	yes
---------------------	-----