

KERN HFA 10T-3

Compact crane scale with integrated display can also be used for tensile force measurement



Measuring system

Adjustment options:	External calibration
Linearity:	10 kg
Precision (of [Max]):	0,200 %
Readability [d]:	5 kg
Recommended adjusting weight:	10000 kg (M3)
Repeatability:	5 kg
Resolution:	2000
Stabilisation time under laboratory conditions:	2 s
Warm up time:	10 min
Weighing capacity [Max]:	10 t
Weighing system:	Strain gauge
Weighing units:	lb N kg

Display

Display digit height (large):	2,300 cm
Display digit height (small):	3 mm

Functions

Data hold function:	yes
---------------------	-----

Environmental conditions

Maximum humidity:	80 %
Maximum operating temperature:	35 °C
Minimum ambient temperature:	5 °C

Power supply

Battery:	3x1.5 V AA
Charging time:	12 h
Input voltage:	100 V - 240 V 50 / 60 Hz
Mains adapter:	Mains adapter external
Mains adapter/adapter included:	EURO CH UK
Operating time:	40 h
Operating time (Backlight off):	30 h
Operating time (Backlight on):	15 h

Services (optional)

Adjustment at the location of installation: 961-252

DAkKS Certificate: 963-133H

Category

Brand:	KERN
Category:	Balances
Product Group:	Crane scale

Packaging & shipping

Delivery:	24 h
Dimensions packaging (WxDxH):	390 x 315 x 125 mm
Gross weight:	6,500 kg
Net weight:	5,500 kg
Shipping method:	Parcel service
UN number:	3496

Construction

Dimensions housing (WxDxH): 90 x 71,6 x 275 mm

Piktogramme

STANDARD



OPTION

