

KERN HFC 600K-1



Compact crane scale for use in harsh environmental conditions or where space is limited, with convenient hand-held terminal



DAkKS Certificate: 963-130H

Category

Brand:	KERN
Category:	Balances
Product Group:	Crane scale

Packaging & shipping

Delivery:	24 h
Dimensions packaging (WxDxH):	500 x 405 x 120 mm
Gross weight:	3,300 kg
Net weight:	1,700 kg
Shipping method:	Parcel service
UN number:	3496

Construction

Casing material:	aluminium
Dimensions housing (WxDxH):	90 x 55 x 255 mm

Piktogramme

STANDARD



OPTION



Measuring system

Adjustment options:	External calibration
Linearity:	400 g
Precision (of [Max]):	0,200 %
Readability [d]:	200 g
Recommended adjusting weight:	500 kg (M3)
Repeatability:	200 g
Resolution:	3000
Stabilisation time under laboratory conditions:	2 s

Warm up time:	10 min
Weighing capacity [Max]:	600 kg
Weighing system:	Strain gauge
Weighing units:	lb N kg

Display

Display digit height (large):	2,300 cm
-------------------------------	----------

Functions

Data hold function:	yes
---------------------	-----

Environmental conditions

Maximum humidity:	80 %
Maximum operating temperature:	35 °C
Minimum ambient temperature:	5 °C

Power supply

Charging time:	12 h
Input voltage:	100 V - 240 V 50 / 60 Hz
Mains adapter:	Mains adapter external
Mains adapter/adaptor included:	EURO CH UK
Operating time:	40 h
Operating time (Backlight off):	30 h
Operating time (Backlight on):	15 h

Services (optional)

Adjustment at the location of installation:	961-250
---	---------