

# KERN HFD10T-3

Robust, high-resolution crane scale up to 12 t



Tare range:	11,995 t
Warm up time:	10 min   10 min   10 min
Weighing capacity [Max]:	3 t   6 t   12 t
Weighing system:	Strain gauge
Weighing units:	kg

Display	
Display digit height (large):	3 cm

Functions	
Standby function:	yes

Environmental conditions	
Maximum humidity:	95 %
Maximum operating temperature:	40 °C
Minimum ambient temperature:	-10 °C
Minimum humidity:	10 %

Power supply	
Battery:	1x12V Type 23A
Charging time:	12 h
Input voltage:	110 V - 240 V AC
Mains adapter:	Mains adapter external
Mains adapter/adaptor included:	EURO CH UK
Operating time (Backlight off):	70 h
Operating time (Backlight on):	30 h

Services (optional)	
Adjustment at the location of installation:	961-252

DAkKS Certificate:	963-133H
--------------------	----------

Category	
Brand:	KERN
Product Group:	Crane scale

Packaging & shipping	
Delivery:	24 h
Dimensions packaging (WxDxH):	725 x 280 x 270 mm
Gross weight:	22,700 kg
Net weight:	21,200 kg
Shipping method:	Parcel service
UN number:	3481

Construction	
Casing material:	Cast aluminium alloys
Dimensions (WxDxH):	194 x 471 x 129 mm
Dimensions of display device (WxDxH):	160 x 120 x 160 mm

Measuring system	
Adjustment options:	External calibration
Linearity:	2 kg   4 kg   10 kg
Precision (of [Max]):	0,200 %
Readability [d]:	1 kg   2 kg   5 kg
Repeatability:	1 kg   2 kg   5 kg
Resolution:	3 3.000 2.400
Stabilisation time under laboratory conditions:	2 s


# KERN HFD10T-3

Robust, high-resolution crane scale up to 12 t



## Piktogramme

### STANDARD



### OPTION



### FACTORY

