

KERN HFD600K-1

Robust, high-resolution crane scale up to 12 t



Tare range:	599,800 kg
Warm up time:	10 min 10 min 10 min
Weighing capacity [Max]:	150 kg 300 kg 600 kg
Weighing system:	Strain gauge
Weighing units:	kg

Display	
Display digit height (large):	3 cm

Functions	
Standby function:	yes

Environmental conditions	
Maximum humidity:	95 %
Maximum operating temperature:	40 °C
Minimum ambient temperature:	-10 °C
Minimum humidity:	10 %

Power supply	
Battery:	1x12V Type 23A
Charging time:	12 h
Input voltage:	110 V - 240 V AC
Mains adapter:	Mains adapter external
Mains adapter/adaptor included:	EURO CH UK US
Operating time (Backlight off):	70 h
Operating time (Backlight on):	30 h

Services (optional)	
Adjustment at the location of installation:	961-250

DAkKS Certificate:	963-130H
--------------------	----------

Category	
Brand:	KERN
Product Group:	Crane scale

Packaging & shipping	
Delivery:	24 h
Dimensions packaging (WxDxH):	725 x 270 x 265 mm
Gross weight:	11 kg
Net weight:	9 kg
Shipping method:	Parcel service
UN number:	3481

Construction	
Casing material:	Cast aluminium alloys
Dimensions (WxDxH):	194 x 471 x 129 mm
Dimensions of display device (WxDxH):	160 x 120 x 160 mm

Measuring system	
Adjustment options:	External calibration
Linearity:	100 g 200 g 400 g
Precision (of [Max]):	0,200 %
Readability [d]:	50 g 100 g 200 g
Repeatability:	50 g 100 g 200 g
Resolution:	3 3.000 3.000
Stabilisation time under laboratory conditions:	2 s


KERN HFD600K-1

Robust, high-resolution crane scale up to 12 t



Piktogramme

STANDARD



OPTION



FACTORY

