

# KERN HFD600K-1IP

Robust, high-resolution crane scale up to 12 t



Tare range:	599,800 kg
Warm up time:	10 min   10 min   10 min
Weighing capacity [Max]:	150 kg   300 kg   600 kg
Weighing system:	Strain gauge
Weighing units:	kg

<b>Display</b>	
Display digit height (large):	3 cm

<b>Functions</b>	
Standby function:	yes

<b>Environmental conditions</b>	
Maximum humidity:	95 %
Maximum operating temperature:	40 °C
Minimum ambient temperature:	-10 °C
Minimum humidity:	10 %

<b>Power supply</b>	
Battery:	1x12V Type 23A
Charging time:	12 h
Input voltage:	110 V - 240 V AC
Mains adapter:	Mains adapter external
Mains adapter/adaptor included:	EURO CH UK
Operating time (Backlight off):	70 h
Operating time (Backlight on):	30 h

<b>Services (optional)</b>	
Adjustment at the location of installation:	961-250

DAkkS Certificate:	963-130H
--------------------	----------

<b>Category</b>	
Brand:	KERN
Product Group:	Crane scale

<b>Packaging &amp; shipping</b>	
Delivery:	24 h
Dimensions packaging (WxDxH):	725 x 270 x 270 mm
Gross weight:	10 kg
Net weight:	8,500 kg
Shipping method:	Parcel service
UN number:	3481

<b>Construction</b>	
Casing material:	Cast aluminium alloys
Dimensions of display device (WxDxH):	187 x 125 x 165 mm
Overall dimensions mounted (WxDxH):	187 x 125 x 420 mm

<b>Measuring system</b>	
Adjustment options:	External calibration
Linearity:	100 g   200 g   400 g
Precision (of [Max]):	0,200 %
Readability [d]:	50 g   100 g   200 g
Repeatability:	50 g   100 g   200 g
Resolution:	3 3.000 3.000
Stabilisation time under laboratory conditions:	2 s


# KERN HFD600K-1IP

Robust, high-resolution crane scale up to 12 t



## Piktogramme

### STANDARD



### OPTION



### FACTORY

