

# KERN HFD6T-3

Robust, high-resolution crane scale up to 12 t



Tare range:	5,998 t
Warm up time:	10 min   10 min   10 min
Weighing capacity [Max]:	1,500 t   3 t   6 t
Weighing system:	Strain gauge
Weighing units:	kg

<b>Display</b>	
Display digit height (large):	3 cm

<b>Functions</b>	
Standby function:	yes

<b>Environmental conditions</b>	
Maximum humidity:	95 %
Maximum operating temperature:	40 °C
Minimum ambient temperature:	-10 °C
Minimum humidity:	10 %

<b>Power supply</b>	
Battery:	1x12V Type 23A
Charging time:	12 h
Input voltage:	110 V - 240 V AC
Mains adapter:	Mains adapter external
Mains adapter/adaptor included:	EURO CH UK
Operating time (Backlight off):	70 h
Operating time (Backlight on):	30 h

<b>Services (optional)</b>	
Adjustment at the location of installation:	961-252

DAkKS Certificate:	963-132H
--------------------	----------

<b>Category</b>	
Brand:	KERN
Product Group:	Crane scale

<b>Packaging &amp; shipping</b>	
Delivery:	24 h
Dimensions packaging (WxDxH):	725 x 270 x 275 mm
Gross weight:	15,800 kg
Net weight:	15 kg
Shipping method:	Parcel service
UN number:	3481

<b>Construction</b>	
Casing material:	Cast aluminium alloys
Dimensions (WxDxH):	194 x 471 x 129 mm
Dimensions of display device (WxDxH):	160 x 120 x 160 mm

<b>Measuring system</b>	
Adjustment options:	External calibration
Linearity:	1 kg   2 kg   4 kg
Precision (of [Max]):	0,200 %
Readability [d]:	500 g   1000 g   2000 g
Repeatability:	500 g   1000 g   2000 g
Resolution:	3 3.000 3.000
Stabilisation time under laboratory conditions:	2 s


# KERN HFD6T-3

Robust, high-resolution crane scale up to 12 t



## Piktogramme

### STANDARD



### OPTION



### FACTORY

