

KERN HFD6T-3IP

Robust, high-resolution crane scale up to 12 t



Tare range:	5,998 t
Warm up time:	10 min 10 min 10 min
Weighing capacity [Max]:	1,500 t 3 t 6 t
Weighing system:	Strain gauge
Weighing units:	kg

Display	
Display digit height (large):	3 cm

Functions	
Standby function:	yes

Environmental conditions	
Maximum humidity:	95 %
Maximum operating temperature:	40 °C
Minimum ambient temperature:	-10 °C
Minimum humidity:	10 %

Power supply	
Battery:	1x12V Type 23A
Charging time:	12 h
Input voltage:	110 V - 240 V AC
Mains adapter:	Mains adapter external
Mains adapter/adaptor included:	EURO CH UK
Operating time (Backlight off):	70 h
Operating time (Backlight on):	30 h

Services (optional)	
Adjustment at the location of installation:	961-252

DAkKS Certificate:	963-132H
--------------------	----------

Category	
Brand:	KERN
Product Group:	Crane scale

Packaging & shipping	
Delivery:	24 h
Dimensions packaging (WxDxH):	720 x 275 x 265 mm
Gross weight:	17 kg
Net weight:	15 kg
Shipping method:	Parcel service
UN number:	3481

Construction	
Casing material:	Cast aluminium alloys
Dimensions of display device (WxDxH):	190 x 130 x 160 mm

Measuring system	
Adjustment options:	External calibration
Linearity:	1 kg 2 kg 4 kg
Precision (of [Max]):	0,200 %
Readability [d]:	500 g 1000 g 2000 g
Repeatability:	500 g 1000 g 2000 g
Resolution:	3 3.000 3.000
Stabilisation time under laboratory conditions:	2 s


KERN HFD6T-3IP

Robust, high-resolution crane scale up to 12 t



Piktogramme

STANDARD



OPTION



FACTORY

