KERN PCB 200-2

The standard in the laboratory





| Measuring system | |
|---|--|
| Adjustment options: | External calibration |
| Linearity: | 20 mg |
| Readability [d]: | 10 mg |
| Recommended adjusting weight: | 200 g (M1) |
| Repeatability: | 10 mg |
| Resolution: | 20000 |
| Stabilisation time under laboratory conditions: | 3 s |
| Warm up time: | 30 min |
| Weighing capacity [Max]: | 200 g |
| Weighing system: | Strain gauge |
| Weighing units: | tl (HK) tol g mo lb dwt ct oz tl (Tw) gn kg ozt |

| Display digit height (large): | 1,500 cm |
|---|----------|
| Counting | |
| Counting resolution: | 10000 |
| Mininum piece weight at piece counting (Laboratory: | 20 mg |
| Mininum piece weight at piece counting (Normal): | 200 mg |

Display

| Functions | |
|--|------|
| Counting function: | yes |
| Percentage determination: | yes |
| Suspended weighing: | Hook |
| Vibration-free weighing (Animal weighing program): | yes |

| Environmental conditions | |
|--------------------------------|-------|
| Maximum humidity: | 80 % |
| Maximum operating temperature: | 35 °C |
| Minimum ambient temperature: | 5°C |

| Power supply | |
|---------------------------------|--------------------------|
| Battery: | 9 V Block |
| Charging time: | 8 h |
| Input voltage: | 100-240V AC 50/60Hz 0.5A |
| Mains adapter: | Mains adapter external |
| Mains adapter/adapter included: | EURO CH UK US |
| Operating time: | 20 h |
| Operating time (Backlight off): | 48 h |
| Operating time (Backlight on): | 24 h |
| Rechargeable battery: | Rchrg. battery optional |

Services (optional)

Adjustment at the location of installation: 961-247

| DALLO O COCCOLO | 000 407 |
|--------------------|---------|
| DAkkS Certificate: | 963-127 |
| | |

| Category | |
|----------------|-------------------|
| Brand: | KERN |
| Category: | Balances |
| Product Group: | Precision balance |

| Packaging & shipping | |
|-------------------------------|--------------------|
| Delivery: | 24 h |
| Dimensions packaging (WxDxH): | 230 x 360 x 180 mm |
| Gross weight: | 1,540 kg |
| Net weight: | 1,020 kg |
| Shipping method: | Parcel service |
| | |

| Construction | |
|-----------------------------|-------------------|
| Casing material: | Plastic |
| Dimensions housing (WxDxH): | 166 x 249 x 83 mm |
| Level indicator: | yes |
| Material weighing plate: | stainless steel |
| Weighing surface (d): | 105 |

KERN PCB 200-2

The standard in the laboratory



Piktogramme

STANDARD



OPTION

