

KERN PFB 600-2



Quick-display precision balance with user-friendly concept of operation - now with larger housing for more secure footing



Measuring system

Adjustment options:	External calibration
Linearity:	30 mg
Readability [d]:	10 mg
Recommended adjusting weight:	600 g (F1)
Repeatability:	10 mg
Resolution:	60000
Stabilisation time under laboratory conditions:	3 s
Tare range:	599,990 g
Warm up time:	2 h
Weighing capacity [Max]:	600 g
Weighing system:	Strain gauge
Weighing units:	g ct

Display

Display digit height (large):	1,500 cm
Display digit height (small):	5 mm

Counting

Counting resolution:	30000
Minimum piece weight at piece counting (Laboratory):	20 mg
Minimum piece weight at piece counting (Normal):	200 mg

Functions

Capacity display:	yes
Counting function:	yes
Function to save totals:	yes
Percentage determination:	yes

Environmental conditions

Maximum humidity:	80 %
Maximum operating temperature:	30 °C
Minimum ambient temperature:	15 °C
Minimum humidity:	0 %

Power supply

Input voltage:	100 V - 240 V 50 / 60 Hz
Mains adapter/adapter included:	EURO CH UK US

Services (optional)

Adjustment at the location of installation: 961-247

DAkKS Certificate:	963-127
--------------------	---------

Category

Brand:	KERN
Category:	Balances
Product Group:	Precision balance

Packaging & shipping

Delivery:	24 h
Dimensions packaging (WxDxH):	375 x 280 x 275 mm
Gross weight:	2,400 kg
Net weight:	2 kg
Shipping method:	Parcel service

Construction

Casing material:	Plastic
Dimensions housing (WxDxH):	210 x 315 x 90 mm
Level indicator:	yes
Material weighing plate:	stainless steel
Overall dimensions mounted (WxDxH):	200 x 240 x 155 mm
Revolving screw feet:	yes
Weighing surface (d):	120

KERN PFB 600-2



Quick-display precision balance with user-friendly concept of operation - now with larger housing for more secure footing

Piktogramme

STANDARD



OPTION



FACTORY

