

KERN PLS1200-3A

High-quality precision scale with comfortable graphic display and enormous weighing range



Measuring system

Adjustment options:	External calibration
Linearity:	3 mg
Minimum weight (USP):	2 g
Readability [d]:	1 mg
Recommended adjusting weight:	1 kg (E2)
Repeatability:	1 mg
Resolution:	1.200.000
Stabilisation time under laboratory conditions:	2 s
Warm up time:	8 h
Weighing capacity [Max]:	1,200 kg
Weighing system:	Force compensation
Weighing units:	tl (HK) g mo lb tl (Singap. Malays) dwt ct oz tl (Tw) gn mg ozt

Display

Display digit height (large):	1,500 cm
Display digit height (small):	4 mm

Counting

Counting resolution:	240000
Minimum piece weight at piece counting (Laboratory):	5 mg
Minimum piece weight at piece counting (Normal):	50 mg
Reference weight:	yes

Functions

Capacity display:	yes
Counting function:	yes
Density determination function:	yes
Percentage determination:	yes
Standby function:	yes
Time display:	yes
Vibration-free weighing (Animal weighing program):	yes
Weighing with tolerance range:	yes

Environmental conditions

Maximum humidity:	80 %
Maximum operating temperature:	35 °C
Minimum ambient temperature:	15 °C

Power supply

Input voltage:	100 V - 240 V 50 / 60 Hz
Mains adapter:	Mains adapter external
Mains adapter/adapter included:	EURO CH AUS UK US

Services (optional)

DAkkS Certificate:	963-103
--------------------	---------

Category

Brand:	KERN
Category:	Balances
Product Group:	Precision balance

Packaging & shipping

Delivery:	24 h
Dimensions packaging (WxDxH):	500 x 360 x 420 mm
Gross weight:	7 kg
Net weight:	4,800 kg
Shipping method:	Parcel service

Construction

Casing material:	Plastic
Dimensions draft shield (ÃxH):	160 70
Dimensions housing (WxDxH):	210 x 345 x 100 mm
Level indicator:	yes
Material weighing plate:	stainless steel
Overall dimensions mounted (WxDxH):	210 x 340 x 160 mm
Revolving screw feet:	yes
Weighing space (ÃxH):	150 60
Weighing surface (d):	110

KERN PLS1200-3A

High-quality precision scale with comfortable graphic display and enormous weighing range



Piktogramme

STANDARD



OPTION

