
KERN RIB10K-3HM







Measuring system	
Adjustment options:	External calibration
Linearity:	2g 5g
Number of weighing ranges:	2
Readability [d]:	2g 5g
Recommended adjusting weight:	10 kg (M1); 5 kg (M1)
Repeatability:	2g 5g
Resolution:	3 3.000
Stabilisation time under laboratory conditions:	2 s
Tare range:	15 kg
Warm up time:	10 min 10 min
Weighing capacity [Max]:	6 kg 15 kg
Weighing system:	Strain gauge
Weighing units:	g kg

Display	
Additional Display possible:	yes
Display digit height (large):	1,800 cm

Technical data about verification	
Minimum load [Min]:	40 g 100 g
Periodic Verification for Italy:	969-112
Verification approval conforming to 2014/31/EU:	yes
Verification by KERN possible:	yes
Verification class:	III
Verification value [e]:	2g 5g

Environmental conditions	
Maximum humidity:	80 %
Maximum operating temperature:	40 °C
Minimum ambient temperature:	-10 °C
Minimum humidity:	0 %

no battery
14 h
100V-240V AC 50/60Hz 0,400 Amax
Mains adapter external
EURO CH UK
80 h
40 h
Rchrg. battery optional - intern

ociviocs (optional)	
Adjustment at the location of installation: 961-2	48

Services (ontional)

DAkkS Certificate:	963-128
Verification:	965-228

Category	
Brand:	KERN
Category:	Balances
Product Group:	Price computing scale

Packaging & shipping	
Delivery:	24 h
Dimensions packaging (WxDxH):	450 x 400 x 210 mm
Gross weight:	5,500 kg
Net weight:	3,800 kg
Shipping method:	Parcel service

Construction	
Casing material:	Plastic
Dimensions housing (WxDxH):	325 x 340 x 115 mm
of stand:	40,500 cm
Level indicator:	yes
Material weighing plate:	stainless steel
Overall dimensions mounted (WxDxH):	325 x 340 x 405 mm
Revolving screw feet:	yes
Weighing surface (WxD):	294 x 225 mm

KERN RIB 10K-3HM



High-quality retail scale with large item memory and user-friendly concept of operation

Piktogramme STANDARD LALEXT MEMORY UNIT 230 V DMS 1 DAY OPTION DAKKS ACCU +3 DAYS FACTORY