

KERN RPB 30K5DHM

Retail scale with memories for item prices



Measuring system

Adjustment options: External calibration

Linearity: 15 g | 30 g

Number of weighing ranges: 2

Readability [d]: 5 g | 10 g

Recommended adjusting weight: 30 kg (M1)

Repeatability: 5 g | 10 g

Resolution: 3 3.000

Resolution (non verifiable): 6000

Resolution (verifiable): 6000

Stabilisation time under laboratory conditions: 1 s

Tare range: -30 kg

Warm up time: 10 min | 10 min

Weighing capacity [Max]: 15 kg | 30 kg

Weighing system: Strain gauge

Weighing units: g kg

Display

Additional Display possible: no

Display digit height (large): 1,500 cm

Technical data about verification

Minimum load [Min]: 100 g

Periodic Verification for Italy: 969-112

Verification approval conforming to 2014/31/EU: yes

Verification by KERN possible: yes

Verification class: III

Verification value [e]: 5 g | 10 g

Environmental conditions

Maximum humidity: 80 %

Maximum operating temperature: 40 °C

Minimum ambient temperature: -10 °C

Minimum humidity: 0 %

Power supply

Battery: no battery

Charging time: 12 h

Input voltage: 220 V - 240 V AC 50 Hz

Mains adapter: Mains adapter external

Mains adapter/adapter included: EURO CH UK US

Operating time (Backlight off): 60 h

Operating time (Backlight on): 30 h

Rechargeable battery: Rchrg. battery optional

Services (optional)

Adjustment at the location of installation: 961-248

DAkkS Certificate: 963-128

Verification: 965-228

Category

Brand: KERN

Category: Balances

Product Group: Price computing scale

Packaging & shipping

Delivery: 24 h

Dimensions packaging (WxDxH): 510 x 330 x 190 mm

Gross weight: 4 kg

Net weight: 3,200 kg

Shipping method: Parcel service

Construction

Casing material: Plastic

Dimensions housing (WxDxH): 313 x 263 x 108 mm

of stand: 48 cm

Level indicator: yes

Material weighing plate: stainless steel

Overall dimensions mounted (WxDxH): 313 x 263 x 480 mm

Revolving screw feet: yes

Weighing surface (WxD): 204 x 263 mm

KERN RPB 30K5DHM

Retail scale with memories for item prices



Piktogramme

STANDARD



OPTION



FACTORY

