## KERN SFB100K-2XL



Stainless steel platform scales with IP65 protection, also with XL platform or EC type approval [M]



Measuring system				
Adjustment options:	External calibration			
Linearity:	20 g			
Load cell connection:	6-wire			
Readability [d]:	10 g			
Recommended adjusting weight:	100 kg (M1)			
Repeatability:	10 g			
Resolution:	10000			
Stabilisation time under laboratory conditions:	2 s			
Tare range:	100 kg			
Warm up time:	30 min			
Weighing capacity [Max]:	100 kg			
Weighing system:	Strain gauge			
Weighing units:	g lb lb:oz Hj. tJ kg			
Display				
Display digit height (large):	5,200 cm			
- <i></i>				

Functions	
Counting function:	yes
Function to save totals:	yes
Vibration-free weighing (Animal weighing program):	yes
Weighing with tolerance range:	yes
Environmental conditions	
Maximum humidity:	95 %
Maximum operating temperature:	40 °C
Minimum ambient temperature:	-10 °C
Minimum humidity:	0 %

Power supply						
Charging time:	12 h					
Input voltage:	110 V - 230 V AC					
Mains adapter:	Mains adapter external					
Mains adapter/adapter included:	EURO CH UK US					
Operating time (Backlight off):	35 h					
Operating time (Backlight on):	20 h					
Services (optional)						
Adjustment at the location of installation: 961-249						
DAkkS Certificate:	963-129					
	905-129					
Category						
Brand:	KERN					
Category:	Balances					
Product Group:	Industiral scale					
Packaging & shipping						
Delivery:	24 h					
Dimensions packaging (WxDxH):	1045 x 675 x 250 mm					
Gross weight:	27,300 kg					
Net weight:						
Not Wolght.	24,500 kg					
Shipping method:	24,500 kg Parcel service					
	-					
Shipping method:	Parcel service					
Shipping method: UN number:	Parcel service					
Shipping method: UN number: Construction	Parcel service 2800					
Shipping method: UN number: Construction Cable length of display device: Dimensions of display device	Parcel service 2800 3 m					
Shipping method: UN number: Construction Cable length of display device: Dimensions of display device (WxDxH): Dimensions of weighing plate	Parcel service 2800 3 m 266 x 165 x 96 mm					
Shipping method: UN number: Construction Cable length of display device: Dimensions of display device (WxDxH): Dimensions of weighing plate (WxDxH):	Parcel service 2800 3 m 266 x 165 x 96 mm 650 x 500 x 142 mm					
Shipping method: UN number: Construction Cable length of display device: Dimensions of display device (WxDxH): Dimensions of weighing plate (WxDxH): Level indicator:	Parcel service 2800 3 m 266 x 165 x 96 mm 650 x 500 x 142 mm yes					
Shipping method: UN number: Construction Cable length of display device: Dimensions of display device (WxDxH): Dimensions of weighing plate (WxDxH): Level indicator: Material weighing plate: Overall dimensions mounted	Parcel service 2800 3 m 266 x 165 x 96 mm 650 x 500 x 142 mm yes stainless steel					
Shipping method: UN number: Construction Cable length of display device: Dimensions of display device (WxDxH): Dimensions of weighing plate (WxDxH): Level indicator: Material weighing plate: Overall dimensions mounted (WxDxH):	Parcel service 2800 3 m 266 x 165 x 96 mm 650 x 500 x 142 mm yes stainless steel 650 x 660 x 590 mm					

## KERN SFB100K-2XL



Stainless steel platform scales with IP65 protection, also with XL platform or EC type approval [M]

## Piktogramme

## STANDARD

КСР	GLP			-√+ ⊙ ?))	666	666	
CAL EXT PROTOCOL	PRINTER	PCS	SUM	TOL	IP 65	IP 67	ACCU
MULTI DMS	1 DAY						

OPTION

DAkks +3 days

FACTORY

