

KERN SFE 60K-2NM

Platform scale with dust and spray protection IP65 and EC type approval [M]



Measuring system

Adjustment options:	External calibration
Linearity:	20 g
Readability [d]:	20 g
Recommended adjusting weight:	60 kg (M1)
Repeatability:	20 g
Resolution:	3000
Stabilisation time under laboratory conditions:	2 s
Warm up time:	10 min
Weighing capacity [Max]:	60 kg
Weighing system:	Strain gauge
Weighing units:	kg

Display

Display digit height (large):	2,200 cm
-------------------------------	----------

Technical data about verification

Minimum load [Min]:	400 g
Periodic Verification for Italy:	969-112
Verification approval conforming to 2014/31/EU:	yes
Verification by KERN possible:	yes
Verification class:	III
Verification value [e]:	20 g

Functions

Function to save totals:	yes
Vibration-free weighing (Animal weighing program):	yes
Weighing with tolerance range:	yes

Environmental conditions

Maximum humidity:	80 %
Maximum operating temperature:	40 °C
Minimum ambient temperature:	-10 °C
Minimum humidity:	0 %

Power supply

Charging time:	12 h
Input voltage:	220 V - 240 V AC 50 Hz
Mains adapter:	Mains adapter external
Mains adapter/adapter included:	EURO UK US
Operating time (Backlight off):	35 h
Operating time (Backlight on):	10 h

Services (optional)

Adjustment at the location of installation: 961-249

DAkkS Certificate:	963-129
Verification:	965-229

Category

Brand:	KERN
Category:	Balances
Product Group:	Industrial scale

Packaging & shipping

Delivery:	24 h
Dimensions packaging (WxDxH):	465 x 790 x 235 mm
Gross weight:	12,700 kg
Net weight:	7,700 kg
Shipping method:	Parcel service
UN number:	3496

Construction

Cable length:	2,500 m
Cable length of display device:	3 m
Dimensions of display device (WxDxH):	210 x 125 x 90 mm
Dimensions of weighing plate (WxDxH):	400 x 300 x 130 mm
Level indicator:	yes
Material weighing plate:	stainless steel
Revolving screw feet:	yes
Wall mount:	yes
Weighing surface (WxD):	400 x 300 mm

KERN SFE 60K-2NM

Platform scale with dust and spray protection IP65 and EC type approval [M]



Piktogramme

STANDARD



OPTION



FACTORY

