## **KERN UFA3T1**

Highly versatile weighing beams (IP67) for large loads to 6 t





Measuring system	
Adjustment options:	External calibration
Linearity:	2 kg
Load cell connection:	6-wire
Readability [d]:	1 kg
Recommended adjusting weight:	3000 kg (M2)
Repeatability:	1 kg
Resolution:	3000
Stabilisation time under laboratory conditions:	2 s
Tare range:	-3 t
Warm up time:	10 min
Weighing capacity [Max]:	3 t
Weighing system:	Strain gauge
Weighing units:	g lb lb:oz oz kg

Display	
Display digit height (large):	5,200 cm
Functions	
Counting function:	yes
Function to save totals:	yes
Vibration-free weighing (Animal weighing program):	yes
Weighing with tolerance range:	yes
Environmental conditions	

Maximum humidity:

Minimum humidity:

Maximum operating temperature:

Minimum ambient temperature:

80 %

40 °C -10 °C

0%

Power supply	
Charging time:	10 h
Input voltage:	110 V - 230 V AC
Mains adapter:	Mains adapter external
Mains adapter/adapter included:	EURO CH UK US
Operating time (Backlight off):	35 h
Operating time (Backlight on):	8 h
Rechargeable battery:	Rchrg. battery optional (factory)
Services (optional)	

DAkkS Certificate:	963-132
Category	
Brand:	KERN
Category:	Balances
Product Group:	Weighing beams
Packaging & shipping	
Delivery:	48 h
Dimensions packaging (WxDxH):	1300 x 480 x 350 mm

59 kg

38 kg

Freight forwarder

Adjustment at the location of installation: 961-252

Gross weight:

Shipping method:

Net weight:

· · · · ·	-
Construction	
Cable length:	5 m
Cable length of display device:	5 m
Dimensions of display device (WxDxH):	250 x 160 x 65 mm
Dimensions of weighing plate (WxDxH):	1200 x 120 x 100 mm
Material weighing plate:	Steel lacquered
Revolving screw feet:	yes
Wall mount:	yes
Weighing surface (WxD):	1200 x 120 mm

## **KERN UFA3T1**





