## KERN UFA6T-3L

Highly versatile weighing beams (IP67) for large loads to 6 t





## Measuring system

<b>U U</b>	
Adjustment options:	External calibration
Linearity:	4 kg
Load cell connection:	6-wire
Readability [d]:	2 kg
Recommended adjusting weight:	6000 kg (M2)
Repeatability:	2 kg
Resolution:	3000
Stabilisation time under laboratory conditions:	2 s
Tare range:	-6 t
Warm up time:	10 min
Weighing capacity [Max]:	6 t
Weighing system:	Strain gauge
Weighing units:	g lb lb:oz oz kg

## Display

Display digit height (large):

Functions	
Counting function:	yes
Function to save totals:	yes
Vibration-free weighing (Animal weighing program):	yes
Weighing with tolerance range:	yes
Environmental conditions	
Maximum humidity:	80 %
Maximum operating temperature:	40 °C
Minimum ambient temperature:	-10 °C
Minimum humidity:	0 %

5,200 cm

Power supply		
Charging time:	10 h	
Input voltage:	110 V - 230 V AC	
Mains adapter:	Mains adapter external	
Mains adapter/adapter included:	EURO CH UK US	
Operating time (Backlight off):	35 h	
Operating time (Backlight on):	8 h	
Rechargeable battery:	Rchrg. battery optional (factory)	
Services (optional)		
Adjustment at the location of installation: 961-252		
DAkkS Certificate:	963-132	
Category		
Brand:	KERN	
Category:	Balances	
Product Group:	Weighing beams	
Packaging & shipping		
Delivery:	48 h	
Dimensions packaging (WxDxH):	2100 x 450 x 370 mm	
Gross weight:	162 kg	
Net weight:	133 kg	
Shipping method:	Freight forwarder	
Construction		
Cable length:	5 m	
Cable length of display device:	5 m	
Dimensions of display device (WxDxH):	250 x 160 x 65 mm	
Dimensions of weighing plate (WxDxH):	2000 x 160 x 100 mm	
Material weighing plate:	Steel lacquered	
Revolving screw feet:	yes	
Wall mount:	yes	

## KERN UFA6T-3L

Highly versatile weighing beams (IP67) for large loads to 6 t



