


# KERN UID3000K-ODM



High-resolution dual-range pallet scale with calibration approval [M] and a large number of data interfaces



## Measuring system

Adjustment options:	External calibration
Linearity:	1,500 kg   3 kg
Load cell connection:	4-wire
Number of weighing ranges:	2
Readability [d]:	500 g   1000 g
Repeatability:	500 g   1000 g
Resolution:	3 3.000
Stabilisation time under laboratory conditions:	4 s
Tare range:	-3 t
Warm up time:	10 min   10 min
Weighing capacity [Max]:	1,500 t   3 t
Weighing system:	Strain gauge
Weighing units:	g lb tJ HJ oz kg PCS

## Display

Display digit height (large):	2,500 cm
Display digit height (small):	2,500 cm

## Technical data about verification

Minimum load [Min]:	10 kg   20 kg
Periodic Verification for Italy:	969-112
Verification approval conforming to 2014/31/EU:	yes
Verification by KERN possible:	yes
Verification class:	III
Verification value [e]:	500 g   1000 g

## Functions

Counting function:	yes
Data hold function:	yes
Percentage determination:	yes
Time display:	yes
Vibration-free weighing (Animal weighing program):	yes
Weighing with tolerance range:	yes

## Environmental conditions

Maximum humidity:	95 %
Maximum operating temperature:	40 °C
Minimum ambient temperature:	-10 °C
Minimum humidity:	10 %

## Power supply

Battery:	no battery
Charging time:	3 h
Input voltage:	100V-240V AC 50/60Hz 0,400 Amax
Mains adapter:	Mains adapter external
Mains adapter/adaptor included:	EURO UK US
Operating time (Backlight off):	43 h
Operating time (Backlight on):	26 h
Rechargeable battery:	Rchrg. battery optional - intern

## Services (optional)

Adjustment at the location of installation: 961-252

DAkkS Certificate:	963-132
Verification:	965-232

## Category

Brand:	KERN
Category:	Balances
Product Group:	Pallet scale

## Packaging & shipping

Delivery:	48 h
Dimensions packaging (WxDxH):	1240 x 890 x 250 mm
Gross weight:	65 kg
Net weight:	44 kg
Shipping method:	Freight forwarder

## Construction

Cable length:	5 m
Cable length of display device:	5 m
Dimensions of display device (WxDxH):	268 x 115 x 80 mm

# KERN UID3000K-ODM




High-resolution dual-range pallet scale with calibration approval [M] and a large number of data interfaces

Dimensions of weighing plate (WxDxH): 1190 x 840 x 110 mm

Level indicator:	yes
Revolving screw feet:	yes
Wall mount:	yes
Weighing surface (WxD):	1195 x 840 mm

## Piktogramme

### STANDARD



### OPTION



### FACTORY

