

KERN MAP80K1

Hand grip dynamometer, e. g. for rehabilitation treatment after accidents



Construction

Dimensions device (WxDxH): 55 x 102 x 212 mm

Piktogramme

STANDARD



OPTION



Measuring system

Readability [d]: 100 g

Weighing capacity [Max]: 80 kg

Weighing units: lb kg

Display

Display digit height (large): 1,200 cm

Environmental conditions

Maximum operating temperature: 35 °C

Minimum operating temperature: 5 °C

Power supply

Battery: CR2450

Operating time: 53 h

Services (optional)

Factory calibration certificate: 961-167

Category

Brand: KERN

Category: Hand grip dynamometers

Packaging & shipping

Delivery: 24 h

Dimensions packaging (WxDxH): 367 x 285 x 100 mm

Gross weight: 1,700 kg

Net weight: 306 g

Shipping method: Parcel service

UN number: 3091