

SENCITY® Spot-S 2x2 WiFi MIMO Antenna 1356.19.0023

Description

Small directional, planar, linear polarized WiFi antenna with 9 dBi gain
 Dual-slant +/- 45° for 2x2 WiFi MIMO antenna configuration
 WLAN IEEE 802.11 a/h/p/n - WiFi band 5.15 - 5.935 GHz
 Rugged design, meets EN 50155 railway and EN 60068 industrial standards
 Fire retardant acc. to EN 45545-2 and NFPA130
 For outdoor and indoor applications
 Ingress protection IP 66 and IP 67

Wall mounting material included



Product Configuration

Technical Data

Electrical Data

	Band 1
Frequency (MHz)	5150 - 5935
VSWR	2
Impedance (Ohm)	50
Gain (dBi)	9
3dB beamwidth (h) (°)	70
3dB beamwidth (v) (°)	60
Composite power max (W)	30
Ambient temperature (°C)	25
Front to back ratio (dB)	20
Vertical electrical tilt (°)	0
Port Isolation (dB)	20

Ports

	Port 1	Port 2
Connector	SMA, jack (female)	SMA, jack (female)
Polarization	-45° slant	+45° slant
DC grounded	Yes	Yes

Connections

	Band 1
Port 1	X
Port 2	X

General Data

Mechanical Data

Dimensions (mm)	101 x 81 x 36 (Height x Width x Depth)
Weight (kg)	0.11
Windload	frontal: 15 N at 160 km/h , Wind speed survival: 220 km/h
Included mounting material	Wall mounting material

Environmental Data

Environmental conditions	indoor/outdoor
Operation temperature (°C)	-40 to 85
Storage temperature (°C)	-40 to 85
Transport temperature (°C)	-40 to 85
Flammability rating	EN 45545-2

SENCITY® Spot-S 2x2 WiFi MIMO Antenna 1356.19.0023

2011/65/EU (RoHS - including 2015/863 and 2017/2102)	compliant
Lead-free soldered	yes
WEEE 2012/19/EU	special marking needed
REACH 1907/2006/EC	compliant

FLAMMABILITY: EN 45545-2 (2013) HL3 and NFPA130 (2013), also BS 6853 and DIN 5510-2

ENVIRONMENT: Meets EN 50155 (2016) and EN 60068 related tests

IP RATING: IP 66 / IP 67 (IEC 60529)

SOLAR RADIATION: EN 50125-3:2004 §4.9, 1120 W/m² for 20h

AIR PRESSURE: EN 50125-3:2004 §4.2, Altitude Class A1 (up to 1400m)

AIR PULE PRESSURE: EN 50125-3:2004 §4.2, 1 kPa/s

RAIN: EN 50125-3:2004 §4.6, delivery rate: 6 mm/min

VIBRATION / SHOCK: EN 50125-3:2004 §4.13, position profile: "outside the track"

POLLUTION: EN 50125-3:2004 §4.11, pollution levels: 4B1, 4S1

CORROSION: MIL-F-14072 E Type 1 "exposed"

MECHANICAL IMPACT (HAMMER IMPACT): EN 60068-2-75 (IEC 62262/2002-02 IK06)

Material Data

Radome colour	RAL 7044 (grey)
Radome material	PC (Polycarbonate)

Related Products

9091.99.0238 Outdoor Spot-S Antenna Down-Sidetilt Bracket

9091.99.0237 L-Bracket for SPOT-S antennas

Related Documents

Mounting instruction	DOC-0000287053
Painting instruction	DOC-0000256180
Security instruction	DOC-0000278984
Outline drawing	DOU-00133337
3D-model	DOC-0000386435

Additional Information

Following Declaration of Conformity for SENCITY Spot-S antennas are available on request: * Industrial standards EN 60068 / EN 60529 / IEC 61373: Ref. DOC-0000318049 * Railway rolling stock, environmental standards EN 50155 and fire behaviour EN 45545-2k, NFPA130: Ref. DOC-0000380375