

## SENCITY® URBAN 100 1399.32.0003

### Description

Outdoor MIMO 2x2 directional antenna for 4G and 5G frequency bands  
2500-2690, 3300-3800, 3800-4200MHz  
Dual slant polarization.  
Very low PIM.  
With NEX10 connectors.



### Product Configuration

### Technical Data

#### Electrical Data

	Band 1	Band 2	Band 3
Frequency (MHz)	2500 - 2690	3300 - 3800	3800 - 4200
VSWR	2	2	2
Gain (dBi)	4	7	7.5
3dB beamwidth (h) (°)	65	65	55
3dB beamwidth (v) (°)	65	65	58
Ambient temperature (°C)			
Front to back ratio (dB)	8	13	14
Port Isolation (dB)	20	20	20

#### Ports

	Port 1	Port 2
Connector	NEX10, jack (female)	NEX10, jack (female)
Polarization	-45° slant	+45° slant

#### Connections

	Band 1	Band 2	Band 3
Port 1	X	X	X
Port 2	X	X	X

#### General Data

IMD level -150 dBc at carrier power 2x 43dBm

#### Mechanical Data

Dimensions (mm) 96 x 117 (Height x Diameter)  
Weight (kg) 0.25

#### Environmental Data

Operation temperature (°C) -40 to 70  
IP rating IP66  
2011/65/EU (RoHS - including 2015/863 and 2017/2102) compliant

#### Material Data

Radome colour RAL 7035 (light-grey)  
Radome material PC (Polycarbonate)

## SENCITY® URBAN 100 1399.32.0003

### Related Products

9091.99.0274 SENCITY® Antenna down- and sidetilt Bracket

9091.99.0238 SPOT-S Antenna Down- and Sidetilt Bracket

### Additional Information

