

Home > All DC Axial

DC Axial Fans - 3110SB-04W-B20 Specifications

[Request Quote](#)

[See Stores](#)


Alternate Part Number: 08025SA-12K-AA

Part Specifications		
Product Type	DC Axial Fans	
Part Number	3110SB-04W-B20-B00	3110SB-04W-B20-E00
Alternate Part Number	08025SA-12K-AA-00	08025SA-12K-EA-00
Rated Voltage	12 (V)	12 (V)
Current	0.050 (A)	0.050 (A)
Air Flow	26.10 (CFM)	26.10 (CFM)
Air Flow	0.740 (m³/min)	0.740 (m³/min)
Mass	80 (g)	80 (g)
Noise	19.0 (dB)	19.0 (dB)
Input Power	0.60 (w)	0.60 (w)
Static Pressure	16.5 (Pa)	16.5 (Pa)
Size [S]	80 (mm)	80 (mm)
Thickness [L]	25.0 (mm)	25.0 (mm)
Speed	2000 (min⁻¹)	2000 (min⁻¹)
Static Pressure	0.070 (H2O)	0.070 (H2O)
PDF	download PDF	download PDF
Termination	Lead	Lead
Bearing Type	Ball	Ball
Sensor	No	No
Lead Wire Count	2	2
Mounting Type	Ribbed	Flange
Lead Wire Type	Standard	Standard

! Our part numbering system has been updated. The specifications and capabilities of this product remain unchanged. The new number for this part is **08025SA-12K-AA**.

3110SB-04W-B20 DC Axial Fans can be an integral part of a cooling solution for your heat-generating applications. Review the part specifications provided to understand how 3110SB-04W-B20 can work with your system. Ready to purchase 3110SB-04W-B20? Explore the inventory currently available through our distributors below. You can also learn about similar DC Axial Fans parts in inventory by following the links provided. Let NMB Technologies Corporation help you find the cooling solutions you need.

- PDFs**
- [08025sa.pdf](#)
- CAD**
- [3110SB-BXX IGES CAD](#)
- [3110SB-BXX Pro-E CAD](#)
- [3110SB-BXX Solidworks CAD](#)
- [3110SB-BXX STEP CAD](#)
- [3110SB-EXX IGES CAD](#)
- [3110SB-EXX Pro-E CAD](#)
- [3110SB-EXX Solidworks CAD](#)
- [3110SB-EXX STEP CAD](#)
- RoHS Certificates**
- [RoHS Cert. for 08025SA-12K-AA-00](#)
- [RoHS Cert. for 3110SB-04W-B20-B00](#)
- [RoHS Cert. for 08025SA-12K-EA-00](#)
- [RoHS Cert. for 3110SB-04W-B20-E00](#)



3110Sb Front
2D CAD Image



3110Sb-Bxx Right Side
2D CAD Image



3110Sb-Exx Right Side
2D CAD Image

Select Store to Purchase

Distributor

In Stock

Click to Call

Similar Parts Available

Part Number

	Yes		Buy It ▶
	Yes		Buy It ▶
	Yes		Buy It ▶
	Yes		Buy It ▶
	Yes		Buy It ▶

3110KL-04W-B10-G00	Part Details >
3110KL-04W-B20-G00	Part Details >
3110KL-04W-B30-D00	Part Details >
3110KL-04W-B40-E00	Part Details >
3110KL-04W-B60-B00	Part Details >
3110KL-04W-B60-G00	Part Details >
3110KL-04W-B69-D00	Part Details >
3110KL-04W-B69-E00	Part Details >
3110KL-05W-B30-G00	Part Details >
3110KL-05W-B50-G00	Part Details >
3110KL-05W-B69-D00	Part Details >
3110SB-04W-B20-E00	Part Details >
3110SB-04W-B30-E00	Part Details >
3110SB-04W-B40-E00	Part Details >
3110SB-04W-B49-E50	Part Details >
3110SB-04W-B50-E00	Part Details >
3110SB-04W-B59-E00	Part Details >
3110SB-05W-B20-E00	Part Details >
3110SB-05W-B40-E00	Part Details >
3110SB-05W-B49-E50	Part Details >
3110SB-05W-B50-E00	Part Details >

Your graphics card does not seem to support WebGL.
Find out how to get it here.