

Detailed Specifications

Frame Width:	92[mm]
Frame Height:	92[mm]
Frame Depth:	25[mm]
Max. Air Flow:	62.5[CFM]
Max. Air Flow:	1.77[m3 per min]
Max. Static Pressure:	0.24[In H2O]
Max. Static Pressure:	61[Pa]
Fan Speed:	3550[RPM]
Noise:	39[dB]
Life Expectancy:	60 degree C 40,000 Hours AA/EA[L10]
Bearing Type:	Ball Bearing
Nominal Voltage:	12[V]
Operating Voltage - Lower:	6[V]
Operating Voltage - Upper:	13.2[V]
Current:	0.23[A]
Input Power:	2.7[W]
Mass:	95[g]