

Home > All DC Axial

## DC Axial Fans - 3110SB-05W-B20 Specifications

[Request Quote](#)

[See Stores](#)

Alternate Part Number: 08025SA-24K-AA

Part Specifications		
Product Type	DC Axial Fans	
Part Number	<b>3110SB-05W-B20-B00</b>	<b>3110SB-05W-B20-E00</b>
Alternate Part Number	<b>08025SA-24K-AA-00</b>	<b>08025SA-24K-EA-00</b>
Rated Voltage	24 (V)	24 (V)
Current	0.030 (A)	0.030 (A)
Air Flow	26.10 (CFM)	26.10 (CFM)
Air Flow	0.740 (m³/min)	0.740 (m³/min)
Mass	80 (g)	80 (g)
Noise	19.0 (dB)	19.0 (dB)
Input Power	0.72 (w)	0.72 (w)
Static Pressure	16.5 (Pa)	16.5 (Pa)
Size [S]	80 (mm)	80 (mm)
Thickness [L]	25.0 (mm)	25.0 (mm)
Speed	2000 (min⁻¹)	2000 (min⁻¹)
Static Pressure	0.070 (H2O)	0.070 (H2O)
PDF	<a href="#">download PDF</a>	<a href="#">download PDF</a>
Termination	Lead	Lead
Bearing Type	Ball	Ball
Sensor	No	No
Lead Wire Count	2	2
Mounting Type	Ribbed	Flange
Lead Wire Type	Standard	Standard

**!** Our part numbering system has been updated. The specifications and capabilities of this product remain unchanged. The new number for this part is **08025SA-24K-AA**.

3110SB-05W-B20 DC Axial Fans can be an integral part of a cooling solution for your heat-generating applications. Review the part specifications provided to understand how 3110SB-05W-B20 can work with your system. Ready to purchase 3110SB-05W-B20? Explore the inventory currently available through our distributors below. You can also learn about similar DC Axial Fans parts in inventory by following the links provided. Let NMB Technologies Corporation help you find the cooling solutions you need.

**PDFs**


[08025sa.pdf](#)

**CAD**

- [3110SB-BXX IGES CAD](#)
- [3110SB-BXX Pro-E CAD](#)
- [3110SB-BXX Solidworks CAD](#)
- [3110SB-BXX STEP CAD](#)
- [3110SB-EXX IGES CAD](#)
- [3110SB-EXX Pro-E CAD](#)
- [3110SB-EXX Solidworks CAD](#)
- [3110SB-EXX STEP CAD](#)

**RoHS Certificates**

- [RoHS Cert. for 08025SA-24K-AA-00](#)
- [RoHS Cert. for 3110SB-05W-B20-B00](#)
- [RoHS Cert. for 08025SA-24K-EA-00](#)
- [RoHS Cert. for 3110SB-05W-B20-E00](#)



**3110Sb Front**  
2D CAD Image



**3110Sb-Bxx Right Side**  
2D CAD Image



**3110Sb-Exx Right Side**  
2D CAD Image

**Select Store to Purchase**

Distributor

In Stock

Click to Call

**Similar Parts Available**

Part Number

	Yes		<a href="#">Buy It ▶</a>
	Yes		<a href="#">Buy It ▶</a>
	Yes		<a href="#">Buy It ▶</a>
	Yes		<a href="#">Buy It ▶</a>
	Yes		<a href="#">Buy It ▶</a>
	Yes		<a href="#">Buy It ▶</a>

3110KL-04W-B10-G00	<a href="#">Part Details &gt;</a>
3110KL-04W-B20-G00	<a href="#">Part Details &gt;</a>
3110KL-04W-B30-D00	<a href="#">Part Details &gt;</a>
3110KL-04W-B40-E00	<a href="#">Part Details &gt;</a>
3110KL-04W-B60-B00	<a href="#">Part Details &gt;</a>
3110KL-04W-B60-G00	<a href="#">Part Details &gt;</a>
3110KL-04W-B69-D00	<a href="#">Part Details &gt;</a>
3110KL-04W-B69-E00	<a href="#">Part Details &gt;</a>
3110KL-05W-B30-G00	<a href="#">Part Details &gt;</a>
3110KL-05W-B50-G00	<a href="#">Part Details &gt;</a>
3110KL-05W-B69-D00	<a href="#">Part Details &gt;</a>
3110SB-04W-B20-E00	<a href="#">Part Details &gt;</a>
3110SB-04W-B30-E00	<a href="#">Part Details &gt;</a>
3110SB-04W-B40-E00	<a href="#">Part Details &gt;</a>
3110SB-04W-B49-E50	<a href="#">Part Details &gt;</a>
3110SB-04W-B50-E00	<a href="#">Part Details &gt;</a>
3110SB-04W-B59-E00	<a href="#">Part Details &gt;</a>
3110SB-05W-B20-E00	<a href="#">Part Details &gt;</a>
3110SB-05W-B40-E00	<a href="#">Part Details &gt;</a>
3110SB-05W-B49-E50	<a href="#">Part Details &gt;</a>
3110SB-05W-B50-E00	<a href="#">Part Details &gt;</a>

Your graphics card does not seem to support WebGL.  
Find out how to get it here.