

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number:

2183231053

Status:

Active

Overview:

DuraClik Connector System

Description:

DuraClik ISL-to-Pigtail Off-the-Shelf (OTS) Cable Assembly, 2.00mm Pitch, Single Row, 600.00mm Length, 5 Circuits, White

Documents:

Drawing (PDF)

Datasheet (PDF)

RoHS Certificate of Compliance (PDF)

General

Product Family

Series

Application

Assembly Configuration

Connector to Connector

Overmolded

Overview

Product Name

Type

UPC

Cable Assemblies

218323

Automotive, Signal, Wire-to-Board

Single Ended Connector

DuraClik ISL-to-Pigtail

No

DuraClik Connector System

DuraClik

Discrete Wire Assembly

195842351851

Physical

Cable Length

Circuits (Loaded)

Color - Resin

Gender

Lock to Mating Part

Material - Metal

Material - Plating Mating

Material - Plating Termination

Material - Resin

Net Weight

Number of Rows

Packaging Type

Pitch - Mating Interface

Single Ended

Termination Interface: Style

Wire Insulation Diameter

Wire Size AWG

Wire/Cable Type

600.00mm

5

White

Female-Pigtail

Yes

Copper Alloy

Tin

Tin

PBT

15.320/g

1

Bag

2.00mm

Yes

Crimp or Compression

1.30mm

22

1x0.35mm² FLRY-A

Electrical

Current - Maximum per Contact

Voltage - Maximum

3.0A

60V AC/DC

Material Info

Reference - Drawing Numbers

Sales Drawing

2183231051-000



EU ELV

Not Relevant

EU RoHS

Compliant

REACH SVHC

Not Contained Per - D(2021)4569-DC (8 July 2021)

Halogen-Free

Status

Not Reviewed

For more information, please visit [Contact US](#)

China RoHS

Green Image

ELV

Not Relevant

RoHS Phthalates

Not Contained

Search Parts in this Series

218323 Series

Mates With

DuraClik Right-Angle Header [502352](#) .

DuraClik Vertical Header [560020](#)

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION