

MUT Series



- **MUT-01A**
- **MUT-03A**

- High SPL
- Small Slim Size
- Tape & Reel Packaging for Auto-Mounting
- Designed for Reflow Process
- Side Sound Port

Specifications:

	MUT-01A	MUT-03A
SPL	Min 85 dB Typ 92 dB	Min 85 dB Typ 93 dB
Rated Voltage	1.5 V _{p-p}	3.0 V _{p-p}
Operating Voltage	Max 1.7 V _{p-p}	Max 4.5 V _{p-p}
Rated Frequency	3200 Hz	
Mean Current Consumption	Max 65 mA	Max 70 mA
Operation Temp.	-20°C to +70°C	
External Size	14 x 11 x 3mm	
Mass	1 g	

