



Main

Product	Buck and Boost Transformer
Enclosure Code	6A
Enclosure Type	NEMA 3R
Insulation Temperature	356 °F (180 °C)
Primary Voltage	120 x 240 V
Power Rating	0.75 kVA
Secondary Voltage	16/32 V
Temperature Rise	115 °C





Ordering and shipping details

Category	16265 - BUCK & BOOST
Discount Schedule	PE2
GTIN	00785901019947
Nbr. of units in pkg.	1
Package weight(Lbs)	17.35 lb(US) (7.87 kg)
Returnability	Yes
Country of origin	MX

Packing Units

Package 1 Height	7.30 in (18.542 cm)
Package 1 width	8.30 in (21.082 cm)
Package 1 Length	8.80 in (22.352 cm)

Offer Sustainability

Sustainable offer status	Green Premium product
California proposition 65	WARNING: This product can expose you to chemicals including: Phenyl glycidyl ether, which is known to the State of California to cause cancer and birth defects or other reproductive harm. For more information go to www.P65Warnings.ca.gov
REACH free of SVHC	Yes
EU RoHS Directive	Compliant  EU RoHS Declaration
Toxic heavy metal free	Yes
Mercury free	Yes
RoHS exemption information	 Yes
China RoHS Regulation	 China RoHS Declaration
Environmental Disclosure	 Product Environmental Profile
PVC free	Yes

Contractual warranty

Warranty	18 months
----------	-----------