



### Main

Product or component type	Dry Sealed Transformer
Primary to Secondary Voltage	480 V delta 208Y/120 V
Full Capacity Taps	2 5 % FCBN

### Complementary

Enclosure Code	14C
Phase	3 phase
Power Rating	9 kVA
Temperature rise	115 °C
Height	14.75 in (374.65 mm)
Width	19.1 in (485.14 mm)
Depth	12.25 in (311.15 mm)
Enclosure mounting	Wall mounted
Net Weight	280.01 lb(US) (127.01 kg)
Enclosure material	Painted sheet steel

### Environment

Enclosure Type	NEMA 3R
Insulation temperature	356 °F (180 °C)
Product certifications	UL Listed CSA CULus

### Ordering and shipping details

Category	16277 - RESIN LVGP XFMR
Discount Schedule	PE2
GTIN	00785901359494
Nbr. of units in pkg.	1
Package weight(Lbs)	280 lb(US) (127.01 kg)
Returnability	Yes
Country of origin	MX

### Packing Units

Package 1 Height	14.80 in (37.592 cm)
Package 1 width	19.30 in (49.022 cm)
Package 1 Length	13.90 in (35.306 cm)

## Offer Sustainability

Sustainable offer status	Green Premium product
California proposition 65	WARNING: This product can expose you to chemicals including: Phenyl glycidyl ether, which is known to the State of California to cause cancer and birth defects or other reproductive harm. For more information go to <a href="http://www.P65Warnings.ca.gov">www.P65Warnings.ca.gov</a>
REACH free of SVHC	Yes
EU RoHS Directive	Compliant <a href="#">EU RoHS Declaration</a>
Toxic heavy metal free	Yes
Mercury free	Yes
RoHS exemption information	<a href="#">Yes</a>
China RoHS Regulation	<a href="#">China RoHS Declaration</a>
Environmental Disclosure	<a href="#">Product Environmental Profile</a>
PVC free	Yes

## Contractual warranty

Warranty	18 months
----------	-----------