


Technical Data Sheet

Model PVLEAD1 Solar MC4 to 4mm Test Lead Set



Features

- Set of black and red MC4 to 4mm adapter test leads for solar applications
- The black lead is a MC4 (female) to 4mm sheathed banana plug on a 60-inch test lead
- The red lead is a MC4 (male) to 4mm sheathed banana plug on a 60-inch test lead
- Allows for connections to test tools that accept 4mm sheathed banana plugs
- · Ensures safe current and voltage measurements on Photovoltaic (PV) modules and systems
- Connect measuring devices to PV power plants, for use in regular tests, measurements, and troubleshooting on solar PV panels
- Nickel plated contacts

Ratings

Voltage: Complies to IEC / EN 61010-031 CAT III 1000V / CAT IV 600V Do Not Disconnect Under Load Current: 20A Temperature Range: +5°C to +40°C (+41°F to +104°F)

Ordering Information

Model: PVLEAD1 MC4 TO 4MM TEST LEAD SET, BLACK/RED

USA: Sales: 800-490-2361 Technical Support: technicalsupport@pomonatest.com Europe: 31-(0) 40 2675 150 International: 425-446-5500 Where to Buy: www.pomonaelectronics.com All dimensions are in inches. Tolerances (except noted): $.xx = \pm .02$ " (,51 mm), $.xxx = \pm .005$ " (,127 mm). All specifications are to the latest revisions. Specifications are subject to change without notice. Registered trademarks are the property of their respective companies.