

# Professional Model 60 to Model 330

## Ratchet Adjustables

Model	Square Drive in	Part Code	Range		Length mm	Weight kg
			N.m	lbf.ft		
60	3/8	11162	8-60	5-45	305	0.6
60	1/2	11172	8-60	5-45	305	0.6
100	3/8	11130	20-100	15-80	340	0.7
100	1/2	11131	20-100	15-80	340	0.7
200	1/2	11132	40-200	30-150	440	1.0
300	1/2	11133	60-300	45-220	560	1.4
330	1/2	11118	60-330	45-250	675	1.4

These professional quality torque wrenches have been designed and precision engineered to match the increasingly stringent demands of modern industry.

- Accuracy of  $\pm 3\%$  of reading exceeds all international standards for torque wrenches.
- Every wrench is supplied with a calibration certificate to satisfy the requirements of ISO 9000.
- The setting lock prevents accidental adjustment during use.
- High quality, reversible ratchets allow work in confined areas. Model 330 has a robust 'push through' ratchet head.
- Dual scale, lbf.ft and N.m, avoids conversion errors.
- Long scale length for foolproof and accurate setting.
- Unmistakable signal is heard and felt when set torque is reached.
- Supplied in a moulded box for protection.
- Also available with a kgf.m or lbf.in scale.

