

U | Contact

Data sheet


PC board jack M12, A-coded, 4-pole, IP67, in unmated condition, potted

Page 1/4

P/N MMT361A715-0009

EAN 4251394631967

2021/09/15 Version: D



See enlarged drawings at the end of document

Product specification

- PC board jack M12
- Front wall mounting
- 4-pole, A-coded according to IEC 61076-2-101
- THR solderable
- Top entry
- Contact carriers black
- IP67 in unmated condition
- suitable for applications in the railway industry





METZ CONNECT

We realize ideas

U Contact

Data sheet PC board jack M12, A-coded, 4-pole, IP67, in unmated condition, potted

Page 2/4

P/N MMT361A715-0009

EAN 4251394631967

2021/09/15 Version: D

Technical Data	
General Data	
Dimensions	
Dimension (D x H)	Ø 16.5 mm x 20.5 mm
Dimension (D x H)	0.65 in. x 0.807 in.
Ports	Single port
Solderability	Acc. to IPC/JEDEC J-STD-020E-MSL 1
Coding	A-coded
Electrical characteristics	
Rated voltage	250 V
Current carrying capacity at 40 °C	4 A
Insulation resistance	min. 100 MOhm
Overvoltage category	II
Degree of pollution	2
Mechanical data	
Material	
Material - Housing	CuZnPb
Material - Contact	CuZnPb
Contact surface	Ni + Au
Material - Insulating body	LCP UL94 V0
Color	black
RoHS	compliant
Life - Number of mating cycles	>= 100
Tightening torque - Plug	0,6 - 1 Nm
Tightening torque - Jack mounting	3 Nm +/- 0,5 Nm
Protection category	IP 67
Climatic properties	
Temperature - Operating °C	-25 °C
Temperature - Operating °C	85 °C
Temperature - Operating °F	-13 °F
Temperature - Operating °F	185 °F

The product meets the following standards

Railway applications	
Electronic equipment used on rolling stock	according to DIN EN 50155
Fire protection on railway vehicles	according to DIN EN 45545-2





CONNECT

We realize ideas

Page 3/4

P/N MMT361A715-0009

EAN 4251394631967

2021/09/15 Version: D

U Contact

Data sheet PC board jack M12, A-coded, 4-pole, IP67, in unmated condition, potted

Technical Data

Classifications	
ETIM 7.0	EC002637
ETIM 8.0	EC002637





CONNECT


We realize ideas

Page 4/4

P/N MMT361A715-0009

EAN 4251394631967

2021/09/15 Version: D



Cut-out

U | Contact

PC board jack M12, A-coded, 4-pole, IP67,

in unmated condition, potted

Data sheet

