

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number: [1053082210](#)
Status: **Active**
Overview: [Nano-Fit Power Connectors](#)
Description: Nano-Fit Receptacle Housing, TPA Capable, 2.50mm Pitch, Dual Row, 10 Circuits, Natural, Glow-Wire Capable

Documents:

3D Model (PDF)	Product Specification PS-105300-100-001 (PDF)
Drawing (PDF)	Application Specification AS-105300-100-001 (PDF)
3D Model	Packaging Specification PK-105308-100-000 (PDF)
Product Specification 1053001000-PS-CH-000 (PDF)	Test Summary 1053000000-TS-000 (PDF)
Product Specification 1053001000-PS-ES-000 (PDF)	Test Summary 1053001000-TS-000 (PDF)
Product Specification 1053001000-PS-JP-000 (PDF)	RoHS Certificate of Compliance (PDF)
Product Specification 1053001000-PS-SK-000 (PDF)	Product Literature (PDF)

Agency Certification

CSA	LR19980
UL	E29179

General

Product Family	Crimp Housings
Series	105308
Application	Power, Wire-to-Board
Comments	Operating temperature is -40#C to +105#C for tin and -40#C to +115#C for gold
Overview	Nano-Fit Power Connectors
Product Name	Nano-Fit
UPC	889056023887

Physical

Circuits (maximum)	10
Color - Resin	Natural
Flammability	94V-0
Gender	Receptacle
Glow-Wire Capable	Yes
Keying to Mating Part	Yes
Lock to Mating Part	Yes
Material - Resin	Nylon
Net Weight	0.900/g
Number of Rows	2
Packaging Type	Bag
Panel Mount	No
Pitch - Mating Interface	2.50mm
Pitch - Termination Interface	2.50mm
Polarized to Mating Part	Yes
Temperature Range - Operating	-40° to +105°C, -40° to +115°C


Electrical

Current - Maximum per Contact	6.5A
-------------------------------	------

Material Info

Reference - Drawing Numbers

Application Specification	AS-105300-100-001
Packaging Specification	PK-105308-100-000
Product Specification	1053001000-PS-CH-000, 1053001000-PS-ES-000, 1053001000-PS-JP-000, 1053001000-PS-SK-000, PS-105300-100-001



Series image - Reference only

EU ELV

Not Relevant

EU RoHS

Compliant

REACH SVHC

Not Contained Per -
D(2021)4569-DC (8
July 2021)

Halogen-Free

Status

Low-Halogen

For more information, please visit [Contact US](#)

China ROHS

ELV

RoHS Phthalates

China RoHS

Green Image

Not Relevant

Not Contained

Search Parts in this Series

[105308](#) Series

Mates With

Nano-Fit Vertical Through Hole Headers
[1053102110](#) , [1053102210](#) , [1053102310](#) ,
[1053122110](#) , [1053122210](#) , [1053122310](#) .
 Nano-Fit Right-Angle Through Hole Headers
[1053142110](#) , [1053142210](#) , [1053142310](#) .
 Nano-Fit Vertical SMT Headers [1054292110](#)
 , [1054292210](#) , [1054292310](#) , [1054292410](#)
 . Nano-Fit Right-Angle SMT Headers
[1054052110](#) , [1054052210](#) , [1054052310](#)
 . Nano-Fit Plug Housings [2014442110](#) ,
[2014442210](#)

Use With

Nano-Fit Crimp Terminal [105300](#)
 Nano-Fit Pre-Crimped Leads (Gold)

[797582129](#) , [797582130](#)
 Nano-Fit Pre-Crimped Leads (Tin)

[797582139](#) , [797582140](#)
 Nano-Fit TPA Retainer
[105325](#)

This document was generated on 10/22/2021

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION