

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number: [0469921410](#)
Status: **Active**
Overview:
Description: Mini-Fit Jr. Receptacle Housing, Dual Row, Nylon 6/6, UL 94V-2, 14 Circuits, Glow-Wire Capable, Black

Agency Certification

CSA LR19980
UL E29179

General

Product Family Crimp Housings
Series [46992](#)
Application Power, Wire-to-Board, Wire-to-Wire
Overview minifit_power_connector_solutions
Product Name Mini-Fit Jr.
UPC 887191637884

Physical

Circuits (maximum) 14
Color - Resin Black
Flammability 94V-2
Gender Receptacle
Glow-Wire Capable Yes
Keying to Mating Part None
Lock to Mating Part Yes
Material - Resin Nylon
Net Weight 2.822/g
Number of Rows 2
Packaging Type Bag
Panel Mount No
Pitch - Mating Interface 4.20mm
Pitch - Termination Interface 4.20mm
Polarized to Mating Part Yes
Ports 1
Stackable No
Temperature Range - Operating -40° to +105°C

Electrical

Current - Maximum per Contact 13.0A

Solder Process Data

Lead-freeProcess Capability N/A

Material Info

Reference - Drawing Numbers

Application Specification 55560001-AS-000
Packaging Specification PK-5557-002-000
Product Specification PS-45750-001-001, PS-5556-001-001
Sales Drawing SD-46992-0000-000
Test Summary 457500003-TS-000, 55560010-TS-000, TS-5556-002-001

EU ELV

Not Relevant

EU RoHS

Compliant

REACH SVHC

Not Contained Per -
D(2021)4569-DC (8
July 2021)

Halogen-Free

Status

Not Low-Halogen

For more information, please visit [Contact US](#)

China ROHS

ELV

RoHS Phthalates

China RoHS

Green Image

Not Relevant

Not Contained

Search Parts in this Series

[46992](#) Series

Mates With

Mini-Fit Jr. Plug [46993](#)

Use With

Mini-Fit Female Crimp Terminal [5556](#) . Mini-Fit Plus HCS Crimp Terminal [45750](#)