

**PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION**

**Part Number:** [5023510301](#)  
**Status:** **Active**  
**Overview:** [DuraClik Connector System](#)  
**Description:** DuraClik Wire-to-Board Receptacle Housing, Single Row, 3 Circuits, Black

**Documents:**

<a href="#">3D Model</a>	<a href="#">Packaging Specification PK-502351-001-001 (PDF)</a>
<a href="#">3D Model (PDF)</a>	<a href="#">Datasheet (PDF)</a>
<a href="#">Drawing (PDF)</a>	<a href="#">RoHS Certificate of Compliance (PDF)</a>
<a href="#">Product Specification PS-502351-001-001 (PDF)</a>	

**General**

Product Family	Crimp Housings
Series	<a href="#">502351</a>
Application	Automotive, Signal, Wire-to-Board
Comments	Molex part has an inner-locking system versus an outer-locking system. Molex part with tail protection feature.
Overview	<a href="#">DuraClik Connector System</a>
Product Name	DuraClik
UPC	887191427249

**Physical**

Circuits (maximum)	3
Color - Resin	Black
Gender	Receptacle
Glow-Wire Capable	No
Keying to Mating Part	Yes
Lock to Mating Part	Yes
Net Weight	0.165/g
Number of Rows	1
Packaging Type	Bag
Panel Mount	No
Pitch - Mating Interface	2.00mm
Polarized to Mating Part	Yes
Temperature Range - Operating	-40° to +105°C


**Electrical**

Current - Maximum per Contact	3.0A
-------------------------------	------

**Material Info**

**Reference - Drawing Numbers**

Packaging Specification	PK-502351-001-001
Product Specification	PS-502351-001-001
Sales Drawing	SD-502351-001-001



Series image - Reference only

**EU ELV**

**Compliant**

**EU RoHS**

**Compliant**

**REACH SVHC**

Not Contained Per -  
D(2021)4569-DC (8  
July 2021)

**Halogen-Free**

**Status**

**Not Low-Halogen**

For more information, please visit [Contact US](#)

China ROHS

ELV

RoHS Phthalates

**China RoHS**

Green Image

Compliant

Not Contained

**Search Parts in this Series**

[502351](#) Series

**Mates With**

DuraClik Header [560020](#) , [502352](#)

**Use With**

Tin-Plated Crimp Terminal AWG 22-26 [560085](#) <br> Tin-Plated Crimp Terminal AWG 24-30 [50212](#) <br> Gold-Plated Crimp Terminal AWG 22-26 [56161](#) <br> DuraClik Pre-Crimped Leads [797581008](#) , [797581009](#)