

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number: [5024391500](#)
Status: **Active**
Overview:
Description: 2.00mm Pitch CLIK-Mate Wire-to-Board Housing, Single Row, Positive Lock, 15 Circuits, White

Agency Certification

UL E29179

General

Product Family Crimp Housings
 Series [502439](#)
 Application Signal, Wire-to-Board
 Comments See Product Specification for maximum current rating by circuit size and wire AWG
 Overview clikmate_wiretoboard_connectors
 Product Name CLIK-Mate
 UPC 822350915939

Physical

Breakaway No
 Circuits (maximum) 15
 Color - Resin White
 Gender Plug
 Glow-Wire Capable No
 Keying to Mating Part Yes
 Lock to Mating Part Yes
 Material - Resin PBT
 Net Weight 955.000/mg
 Number of Rows 1
 Packaging Type Bag
 Panel Mount No
 Pitch - Mating Interface 2.00mm
 Polarized to Mating Part Yes
 Stackable No
 Temperature Range - Operating -40° to +105°C

Electrical

Current - Maximum per Contact 3.0A

Material Info

Reference - Drawing Numbers

Application Specification AS-502439-001-001, AS-502439-002-001
 Packaging Specification 5024399200-200
 Product Specification 5024431570-000
 Sales Drawing 5024391500-000

EU ELV

Not Relevant

EU RoHS

Compliant

REACH SVHC

Not Contained Per -
 D(2021)4569-DC (8
 July 2021)

Halogen-Free

Status

Not Low-Halogen

For more information, please visit [Contact US](#)

China ROHS

ELV

RoHS Phthalates

China RoHS

Green Image

Not Relevant

Not Contained

Search Parts in this Series

[502439](#) Series

Mates With

[502443](#) PCB Receptacle Vertical . [502494](#)
 PCB Receptacle Right Angle

Use With

CLIK-Mate Terminal [502438](#)
 CLIK-Mate Pre-Crimped Leads [797581014](#) , [797581015](#)