

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number: [0349590341](#)
Status: **Active**
Overview: [Mini50 Connection Systems](#)
Description: Mini50 Unsealed Receptacle, 3 Rows, with CPA, 34 Circuits, Polarization Option B, Gray

Documents:

3D Model (PDF)	Application Specification AS-34959-001-001 (PDF)
Drawing (PDF)	Packaging Specification PK-31301-538-001 (PDF)
3D Model	Test Summary TS-34961-001-001 (PDF)
Product Specification PS-34959-001-001 (PDF)	RoHS Certificate of Compliance (PDF)
Application Specification 349590001-AS-CH-000 (PDF)	Product Literature (PDF)

General

Product Family	Crimp Housings
Series	34959
Application	Automotive, Power, Wire-to-Board
Overview	Mini50 Connection Systems
Polarization	B
Product Name	Mini50
UPC	887191704425


Physical

Circuits (maximum)	34
Color - Resin	Gray
Gender	Receptacle
Glow-Wire Capable	No
Keying to Mating Part	Yes
Lock to Mating Part	Yes
Material - Resin	Nylon
Net Weight	5.524/g
Number of Rows	3
Packaging Type	Bag
Panel Mount	No
Pitch - Mating Interface	2.00mm
Pitch - Termination Interface	2.00mm
Polarized to Mating Part	Yes
Stackable	No
Temperature Range - Operating	-40° to +105°C

Material Info

Reference - Drawing Numbers

Application Specification	349590001-AS-CH-000, AS-34959-001-001
Packaging Specification	PK-31301-538-001
Product Specification	PS-34959-001-001
Sales Drawing	SD-34959-030-001
Test Summary	TS-34961-001-001



Series image - Reference only

EU ELV

Compliant

EU RoHS

Compliant

REACH SVHC

Not Contained Per -
D(2021)4569-DC (8
July 2021)

Halogen-Free

Status

Low-Halogen

For more information, please visit [Contact US](#)

China ROHS	Green Image
ELV	Compliant
RoHS Phthalates	Not Contained

Search Parts in this Series

[34959](#) Series

Mates With

Mini50 Vertical Headers:
 [349580341](#)
, [349587341](#) , [349588341](#)
Mini50
Right-Angle Headers:
 [349610341](#) ,
[349617341](#) , [349618341](#)

Use With

CTX50 Unsealed Terminals [560023](#)